





客户确认  
日期



规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating  
1.5A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触阻抗: Contact Resistance  
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:  
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:  
1000MΩ ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Umate Force  
Mate force: 3.75kgf(MAX)  
Umate force: 1.02kgf(MIN)
2. 端子保持力: Terminal Retention  
1.2kgf(MIN)

原材料: Material:

1. 塑胶: Housing:  
Hing Temperature Thermoplastics,  
UL 94V-0 PBT/LCP White/Black
  2. 端子: Contact: Copper Alloy C2680
  3. 外壳: Shell: Copper Alloy C2680/SPCC
- 电镀: Finish:  
1. 端子: Contact: Plated Gold in Mating Area:  
Tin On Solder Falls  
2. 外壳: Shell:  
Nickel Plating

APPROVED:

DATE:

CHECKED:

DATE:

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

DRAWN:

DATE:

SXA

2019-05-18

TITLE:

深圳市灿科盟实业有限公司  
CHANKEMENG INDUSTRY CO., LTD

USB-A/F-14P 180° 贴片 SMT 卷边 定位柱.2 10P本色

CLIENT P/N U-USBAM04P-F000

UNIT	mm	SCALE	Free	REV. A	HLW0
FILE NO.	Chantw-USB-00007				