





客户确认  
日期



**规格说明: Specifications:**

**电气特性: Electrical:**

1. 额定电流: Current Rating  
1.5A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触电阻: Contact Resistance  
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:  
500 V AC For one minute
5. 绝缘电阻: Insulation Resistance:  
1000MΩ@ 25°C

**原材料: Raw material:**

1. 塑胶: Plastic cement:  
Hing Temperature Thermoplastics,  
PBT/LCP White/Black
  2. 端子: Contact: Copper Alloy C2680/C5191
  3. 外壳: shell: SPC/Copper Alloy C2680
- 电镀: Electroplate:**
1. 端子: Contact: Plated Gold in Mating Area:  
Tin On Solder Tails
  2. 外壳: Shell:  
Nickel Plating

**TOLERANCE TABLE**

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:

DATE:

CHECKED:

DATE:

DRAWN:

DATE:

SXA

2019-05-18

**TITLE:**

USB-A/P-1\*4P H=15.0mm 180度直插 直脚

**深圳市灿科盟实业有限公司**  
CHANKEMENG INDUSTRY CO., LTD

PROD. P/N U-USBAS04P-F000

UNIT	mm	SCALE	Free	REV.	
FILE NO.	Chantw-USB-00075	REV.		HL/NO	