






客户确认
日期



RECOMMENDED PCB LAYOUT
(TOL: ±0.05)

规格说明: Specifications:
电气特性: Electrical:

- 1. 额定电流 Current Rating 1.0A/contact terminal
 - 2. 额定电压 Voltage Rating 30V DC
 - 3. 接触阻抗: Contact Resistance 50 milliohms Max
 - 4. 耐电压: Dielectric Withstanding Voltage 300 V AC AT Sea Level
 - 5. 绝缘阻抗: Insulation Resistance 100MEGA ohms MIN
- 原材料: Raw material:
- 1. 塑胶: Plastic cement Hing Temperature Thermoplastics, UL 94V-0 LCP Black
 - 2. 端子: Contact: Copper Alloy C5191
 - 3. 外壳: Shell: Copper Alloy C2680 电镀: Electroplate:
 - 1. 端子: Contact: Plated Gold in Mating Area Tin On Solder Tails
 - 2. 外壳: Shell: Nickel Plating

APPROVED:	DATE:	TITLE: 深圳市灿科盟实业有限公司 C kintw CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	Micro usb 5P 2型 SMT 四脚加长插板 带挂 卷边			
DRAWN:	DATE:	CLIENT P/N	U-MICROM5P-BF13	UNIT	mm
SXA	2019-05-22	SCALE	Free	REV.	A
TOLERANCE TABLE		FILE NO.	/		
.0	±0.30				
.00	±0.20				
.000	±0.05				