



MECHANICAL

Insulator material:
 PBT@glass-fibre reinforced
 UL 94V-0
 plastic:Brass
 Nut specifications:
 Shell:nicdel (or tin,gold)plated
 Number of contact:04.
 Durabil tty:5000 cycles

ELECTRICAL

Current rating:5Amp
 Dielectric withstanding voltage:AC
 500Vmin(500v dc)
 500m max
 Contactresistance:
 25m max
 Working temperayure:-50° c--+
 150° c

NOTES:

1. 产品外观不得有压伤，缩水，缺胶等不良。毛边不大于0.05mm
2. 产品组装后无不导通现象。
3. 产品材质. 端子: C2680, T=0.20mm、外壳: Spcc, T=0.30mm
 胶壳: PP
4. 电镀规格: 端子镀半金锡1U', 外壳镀镍100U', .24H

APPROVED:	DATE:	TITLE: USB-A-M-4P 焊线一件式 铁壳 白胶 端子镀金 加长款			
CHECKED:	DATE:	CLIENT	P/N	SCALE	REV.
DRAWN: SXA	DATE: 2019-04-27	U-USBAW04P-M004	mm	free	A
TOLERANCE TABLE		UNIT	SCALE	free	REV.
.0	±0.20	mm			
.00	±0.10				
.000	±0.05	FILE NO.			

深圳市灿科盟实业有限公司
 GkmtwCHANKLEMENT INDUSTRYCO., LTD