



**技术参数 SPECIFICATIONS**

间距 (Pitch) : 1.0mm  
 极数 (Poles) : 2~29  
 额定电压 (Voltage rating) : 50V DC/AC  
 额定电流 (Current rating) : 0.5A DC/AC  
 耐压值 (Withstand Voltage) : 500V  
 工作温度 (Working Temperature) : -25℃~+85℃  
 绝缘电阻 (Insulation Resistance) : ≥500MΩ  
 接触电阻 (Contact resistance) : ≤30mΩ  
 单面接触 (Single contact)

**材料 Material**

接触件 (Contact) : 磷青铜 t=0.20 镀亚锡 Phosphor Bronze Tin-plated  
 焊片 (solder tab) : 黄铜 t=0.20 镀亚锡 Brass Tin-plated  
 塑胶主体 (Housing) : LCP耐热树脂 (UL94V-0) LCP-Heat resistance plastic (UL94V-0)  
 后盖 (Slider) : LCP耐热树脂 (UL94V-0) LCP-Heat resistance plastic (UL94V-0)

**规格尺寸**

孔位	A	B	C
2P	1.0	3.1	6.8
3P	2.0	4.1	7.8
4P	3.0	5.1	8.8
5P	4.0	6.1	9.8
6P	5.0	7.1	10.8
7P	6.0	8.1	11.8
8P	7.0	9.1	12.8
9P	8.0	10.1	13.8
10P	9.0	11.1	14.8
11P	10.0	12.1	15.8
12P	11.0	13.1	16.8
13P	12.0	14.1	17.8
14P	13.0	15.1	18.8
15P	14.0	16.1	19.8
16P	15.0	17.1	20.8
17P	16.0	18.1	21.8
18P	17.0	19.1	22.8
19P	18.0	20.1	23.8
20P	19.0	21.1	24.8
21P	20.0	22.1	25.8
22P	21.0	23.1	26.8
23P	22.0	24.1	27.8
24P	23.0	25.1	28.8
25P	24.0	26.1	29.8
26P	25.0	27.1	30.8
27P	26.0	28.1	31.8
28P	27.0	29.1	32.8
29P	28.0	30.1	33.8

APPROVED: DATE:  
 CHECKED: DATE:  
 DRAWN: DATE:  
 LYF 2017-11-17

**Ckmtw** 深圳市灿科盟实业有限公司  
 CHANKLEMENT INDUSTRY CO., LTD  
 TITLE: FPC1.0mm-XP 下接 翻盖式  
 PROD. P/N /  
 UNIT mm SCALE free  
 FILE NO. Ckmtw-FPC-0050 REV. B LX00

**TOLERANCE TABLE**

.0	±0.30
.00	±0.20
.000	±0.05