

钳位滤波器(带包装盒铁氧体磁芯)

ZCAT12V-BK









用途	车载等级
产品型	车载型
适用电缆	Ф 12mm
系列	ZCAT-V
状态	量产体制



	占 4	
A	$34.60 \text{mm} \pm 1.50 \text{mm}$	
В	12.00mm ± 1.50 mm	
C	$27.50 \text{mm} \pm 1.50 \text{mm}$	
D	27.00mm ±1.50mm	
Е		

	电气特性	
阻抗 (Min.) / Ω	140 at 100MHz	

	其他
使用温度范围	-40 to 125° C
AEC-Q200	Yes
Case Color	黑
包装个数	120pcs
重量	44. 4g

[!] Images are for reference only and show exemplary products.

[!] This PDF document was created based on the data listed on the TDK Corporation website.

[!] All specifications are subject to change without notice.

钳位滤波器(带包装盒铁氧体磁芯)

ZCAT12V-BK










特性图表(这是参考数据,并不保证产品的特性。)



[!] Images are for reference only and show exemplary products.

[!] This PDF document was created based on the data listed on the TDK Corporation website.

[!] All specifications are subject to change without notice.

钳位滤波器(带包装盒铁氧体磁芯)

ZCAT12V-BK










Associated Images



[!] Images are for reference only and show exemplary products.

[!] This PDF document was created based on the data listed on the TDK Corporation website.

[!] All specifications are subject to change without notice.