



客户确认
日期



RECOMMENDED P.C.B PATTERN LAY OUT

- Specifications:
- Electrical:
1. Current Rating
1.5A/contact terminal
 2. Voltage Rating
30V DC
 3. Contact Resistance
30 milliohms MAX
 4. Dielectric Withstanding Voltage:
500 V AC AT Sea Level
 5. Insulation Resistance:
1000MEGA ohms MIN
- Mechanical:
1. Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX)
Unmate force: 1.02kgf(MIN)
 2. Terminal Retention
1.2kgf(MIN)
- Material:
1. Housing:
Hing Temperature Thermoplastics
PBT White/Black
 2. Contact: Copper Alloy C2680
 3. Shell: Copper Alloy C2680/SPCC
- Finish:
1. Contact: Plated Gold in Mating Area
Tin Dn Solder Tails
 2. Shell:
Nickel Plating

APPROVED:	DATE:	 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD	
CHECKED:	DATE:	TITLE: USB-A/F-1*4P 双层 190度直插14.2 无脚 自嵌式 无焊片 (双触脚)	
TOLERANCE TABLE		CLIENT P/N	U-USBAS04P-F200
.0	±0.20	UNIT	mm
.00	±0.10	SCALE	Free
.000	±0.05	FILE NO.	Chant-USB-00081
DRAWN:	DATE:	REV.	A
SXA	2019-07-24	REV.	A