



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:—25℃~80℃
 Operating force:3—20N
 Operating Life:5,000cycles

Model NO	PJ-316A-A	PJ-316A-B	PJ-316A-C
Schematic			
Model NO	PJ-316A-D	PJ-316A-E	PJ-316A-F
Schematic			

②	Shunt terminal	6	Phosphor bronze	Plating Au		
①	Housing	1	PPA	Black		
ITEM	PART NAME	Serial number	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE	ELECTRONICS CO.,LTD			
DRAWN		QIFENG.XU	2014/9/19	PHONE JACKES		
CHECKED				PJ-316A		
APPROVALS				SCALE: 1:1		
TOLERANCES ARE		30~0.1±	±0.30	ANGLE	PROJ:	
		10~0.30	±0.20	UNIT: mm	SHEET 1 OF 1	
		5~10	±0.15	DRAWING NO.		
		~5	±0.10			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			