



P. C. B Layout

一. 电气性能:

- 1-1. 额定电流: 3A AC DC.
- 1-2. 接触电阻: ≤20mΩ
- 1-3. 绝缘电阻: ≥1000MΩ
- 1-4. 耐压: 550V AC/Minute

二. 物理特性:

- 2-1. 操作温度: -55℃~105℃
- 2-2. 焊接温度: +220℃, 10s max

三. 材质:

- 3-1. 塑胶: PBT(Black) UL94V-0
- 3-2. 插针: Brass/Gold plated

| PIN | A | B |
|-----|--------|-------|
| 1 | 2.54 | 0.00 |
| 2 | 5.08 | 2.54 |
| 3 | 7.62 | 5.08 |
| 4 | 10.16 | 7.62 |
| 5 | 12.70 | 10.16 |
| 6 | 15.24 | 12.70 |
| 7 | 17.78 | 15.24 |
| 8 | 20.32 | 17.78 |
| 9 | 22.86 | 20.32 |
| 10 | 25.40 | 22.86 |
| 11 | 27.94 | 25.40 |
| 12 | 30.48 | 27.94 |
| 13 | 33.02 | 30.48 |
| 14 | 35.56 | 33.02 |
| 15 | 38.10 | 35.56 |
| 16 | 40.64 | 38.10 |
| 17 | 43.18 | 40.64 |
| 18 | 45.72 | 43.18 |
| 19 | 48.26 | 45.72 |
| 20 | 50.80 | 48.26 |
| 21 | 53.34 | 50.80 |
| 22 | 55.88 | 53.34 |
| 23 | 58.42 | 55.88 |
| 24 | 60.96 | 58.42 |
| 25 | 63.50 | 60.96 |
| 26 | 66.04 | 63.50 |
| 27 | 68.58 | 66.04 |
| 28 | 71.12 | 68.58 |
| 29 | 73.66 | 71.12 |
| 30 | 76.20 | 73.66 |
| 31 | 78.74 | 76.20 |
| 32 | 81.28 | 78.74 |
| 33 | 83.82 | 81.28 |
| 34 | 86.36 | 83.82 |
| 35 | 88.90 | 86.36 |
| 36 | 91.44 | 88.90 |
| 37 | 93.98 | 91.44 |
| 38 | 96.52 | 93.98 |
| 39 | 99.06 | 96.52 |
| 40 | 101.60 | 99.06 |

图名: PZ2. 54-2xNAW
-PC6. 0MM

图号: 4PZ2542XXAW1491010

未标注公差

| | | | |
|-----|-------|------|-----|
| XX. | ±0.40 | XX.° | ±2° |
| X. | ±0.30 | .XX° | ±1° |
| .X | ±0.20 | | |
| .XX | ±0.15 | | |

绘制: 韩金锋 单位: MM

签发: 比例: 1:1

审核: 视图: