






REV.	EQ. NO.	DESCRIPTION	DATE	DESIGN



Poles	Dimensions	
	A	B
02	2.00	6.00
03	4.00	8.00
04	6.00	10.00
05	8.00	12.00
06	10.00	14.00
07	12.00	16.00
08	14.00	18.00
09	16.00	20.00
10	18.00	22.00
11	20.00	24.00
12	22.00	26.00
13	24.00	28.00
14	26.00	30.00
15	28.00	32.00



SPECIFICATIONS

- 1) MATERIAL:
HOUSING: GLASS FILLED PA66 UL94V0
TERMINAL: PHOSPHOR BRONZE, TIN PLATING
- 2) Current rating: 2A AC, DC.
- 3) VOLTAGE RATING: 100V AC/DC
- 4) CONTACT RESISTANCE: 20M OHMS MAX
- 5) INSULATION RESISTANCE: 800M OHMS MIN.
- 6) TEMPERATURE RANGE: $-40^{\circ} \sim +105^{\circ}$.

DIM	TOL	DIM	TOL
X	/	X	/
XX	0.25	XX	/
XXX	0.15	XXX	/
KXXX	0.10	KXXX	/

CNJM Joint More Precision electronics Co., Ltd.

DRAW NO.	DATE	P/N NO:	DRAW NAME:
DESIGN: 陈雪峰	2019.1.20	A2004WV-NP	2.0mm pitch 180° wafer
CHECK: 杨焯			
REVIEW:			

REV. A/1 SCALE 1:1 UNIT: mm SHEET: 1 OF 1