


NOTE:

1. HSF:HSF CONCRRAFT LEVEL1
2. MATERIAL:
HOUSING :HIGH-TEMPERATURE PLASTIC,COLOR:BLACK,UL 94 V-0
TERMINAL:COPPER ALLOY
- 3.FINISH:
TERMINAL:
NICKEL UNDERPLATING ALL OVER BASE MATERIAL
CONTACT AREA : GOLD FLASH PLATING OVER UNDERPLATE
SOLDER AREA : GOLD FLASH PLATING OVER UNDERPLATE
4. INSPECTION SYMBOL:
● : MANUFACTURER INSPECTION
◆ : Q.C INSPECTION



H-H (4:1)

				GENERAL TOLERANCE		DRAW:	PART NO:
				X. ±0.30	X.° ± 2.00°	Allen Ma	106322BE75C
				.X ±0.20	.X° ± 1.00°	CHECKED:	TITLE:
				.XX ±0.10	.XX° ± 0.50°		MXM 3 CONNECTOR 0.50PITCH 314PIN
				.XXX ±0.05		APPROVE:	DRAWING NO:
				UNITS: mm	SHEET: 1 / 3		106322BE75C
8	B	E130581A	Allen Ma	12/11/2013			
8	A	E130291A	Allen Ma	07/03/2013			
	REV.	ECO NO.	DRAW	DATE			
	MATERIAL: SEE NOTES	FINISH: SEE NOTES	DATE: 12/11/2013	REV. B			



Kun Shan Dragonstate Electronic Technology Co.,LTD

A

B

C

D

E

F

Halogen Free

1

2

3

4

5

6

7

1

2


3

4

5

6

7



GENERAL TOLERANCE

DRAW:

PART NO:

X. ± 0.30 X° ± 2.00°

Allen Ma

106322BE75C

.X ± 0.20 .X° ± 1.00°

CHECKED:

TITLE:

.XX ± 0.10 .XX° ± 0.50°

APPROVE:

MXM3 CONNECTOR
0.50PITCH 314PINUNITS:
mmSHEET:
2 / 3

DRAWING NO:

106322BE75C

REV. ECO NO. DRAW DATE

REV. B

MATERIAL:
SEE NOTESFINISH:
SEE NOTESDATE:
12/11/2013

CONCRAFT

Kun Shan Drangonstate Electronic Technology Co.,LTD

A


B

C

D

E

F



RECOMMENDED P.C.B LATOUT (PER PIN)
TOP VIEW (1.6:1)

				GENERAL TOLERANCE		DRAW: Allen Ma	PART NO: 106322BE75C
				X. ± 0.30	X° $\pm 2.00^\circ$	CHECKED:	TITLE: MXM3 CONNECTOR 0.50PITCH 314PIN
				.X ± 0.20	.X° $\pm 1.00^\circ$		
				.XX ± 0.10	.XX° $\pm 0.50^\circ$		
				.XXX ± 0.05		APPROVE:	DRAWING NO: 106322BE75C
8	A	E130291A	Allen Ma	07/03/2013	UNITS: mm	SHEET: 3 / 3	
	REV.	ECO NO.	DRAW	DATE		 Kun Shan Drangonstate Electronic Technology Co.,LTD	
	MATERIAL: SEE NOTES	FINISH: SEE NOTES	DATE: 12/11/2013	REV. B			