


RECOMMENDED P.C.B LAYOUT

**MATERIAL**  
 Insulator: PA6T UL94V-0  
 Contact pin: Brass  
 Contact plated: Gold Flash All Over Nickel

**Specification**  
 Current Rating : 3Amp  
 Insulation Resistance : 1000MΩ Min  
 Contact Resistance: 20 Milliohms Max  
 Dielectric withstanding Voltage: AC 500V  
 Operation Temperature : -40℃ ~ +105℃



核准:	业务:	日期:	 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD
YAN	YAN	2011-01-26	
未注公差表	客户料号	品名规格:	210R-1*8P (3.5/4.8/2.54/3.0)
X.X ±0.2 X.XX ±0.10 X.XXX ±0.050	单位 mm	比例 /	
	图纸编号: S007200247	版本 A	