



Material:
 Insulator: PBT+30% Glass Fiber (UL94V-0).
 Contact: Copper Alloy.
 Contact Plated: Gold or Tin over Nickel Plated.
 Specification:
 Current Rating: 1 Amp.
 Withstanding Voltage: AC 500V for 1 Minute.
 Insulation Resistance: 1000M Min. at DC 500V.
 Contact Resistance: 15m Max..
 Operating Temperature: -40°C ~ +105°C.

Pos.	Part No.	Dim. A	Dim. B	Dim. C	Dim. D	Dim. E	Dim. F
8	300F-8P有耳	7.62	15.61	20.41	8.89	25.26	34.46
10	300F-10P有耳	10.16	18.15	22.95	11.43	27.80	37.00
14	300F-14P有耳	15.24	23.23	28.03	16.51	32.88	42.08
16	300F-16P有耳	17.78	25.77	30.57	19.05	35.42	44.62
20	300F-20P有耳	22.86	30.85	35.65	24.13	40.50	49.70
24	300F-24P有耳	27.94	35.93	40.73	29.21	45.58	54.78
26	300F-26P有耳	30.48	38.47	43.27	31.75	48.12	57.32
30	300F-30P有耳	35.56	43.55	48.35	36.83	53.20	62.40
34	300F-34P有耳	40.64	48.63	53.43	41.91	58.28	67.48
40	300F-40P有耳	48.26	56.25	61.05	49.53	65.90	75.10
50	300F-50P有耳	60.96	68.95	73.75	62.23	78.60	87.80
60	300F-60P有耳	73.66	81.65	86.45	74.93	91.30	100.50
64	300F-64P有耳	78.74	86.73	91.53	80.01	96.38	105.58

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE: 300F-XP 压线式 有耳 灰白色
SXA	2019-02-20	CLIENT P/N: B-3000FXXP-E800
		UNIT: mm
		SCALE: Free
		FILE NO. Ckintw-300-0008
		REV. A Q102