


客户确认	
日期	



4	ID
3	D+
2	D-
1	VBUS

PIN NUMBER	SIGNAL NAME
4	ID
3	D+
2	D-
1	VBUS

PCB LAYOUT

NOTES:

- 1.MATERIAL:
 1.1 Housing:thermoplastic plastics
 1.2 terminals:Copper Alloy
 Gold plated in contact area:
 Tin plated in termination
 Nickel Plated overall
 1.3 Shell:Steel&Copper Alloy
 Nickel Plated overall
- 2.ELECTRICAL CHARACTERISTICS:
 2.1 Rating Current :1.5 Ampere
 2.2 Rating Voltage :30 V Max
 2.3 Contact Resistance:30 Milli ohms
 2.4 Insulation Resistance:1000 Mega ohms Min.
- 3.MECHANICAL CHARACTERISTICS:
 3.1 Connector Mating force: 35N MAX(3.57Kg_f)
 3.2 Connector Unmating force:10N min(1.02Kg_f)
 3.3 Durability:1500Cycles.
 4.ENVIRONMENT CHARACTERISTICS:
 4.1 Operating temperature:-0℃ to + 50℃
 4.2 Storage temperature:-20℃ to + 60℃

APPROVED:	DATE:	C 深圳市灿科盟实业有限公司 CANTON CHANKEMENG INDUSTRY CO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE: USB-A-M-1*4P 公头 弯插 引脚弯插 白胶
SXA	2019-5-31	PART P/N U-USBAR04P-M002
TOLERANCE TABLE		UNIT mm SCALE free
.0	±0.20	FILE NO. Canton-USB-A-0002
.00	±0.10	REV. A
.000	±0.05	ELMO