

电气性能/Electrical

参考标准/Standard: UL IEC
 额定电压/Rated voltage: 300V 320V
 额定电流/Rated current: 15A 20A
 接触电阻/Contact resistance: 20mΩ
 使用线径/Wire range: 28-14AWG 2.5mm²
 耐电压/Withstanding voltage: AC2000V/1Min
 绝缘电阻/Insulation resistance: 500MΩ/DC500V

机械性能/Mechanical

温度范围/Temp.Range: -40°C~+105°C
 扭矩/Torque: 0.5Nm(4.5lb`in)
 剥线长度/Strip length: 7-8mm


尺寸/Dimensions

间距/Pitch: 7.5mm,7.62mm
 极数/Poles: 2P-24P

材质及电镀/Material

塑件/Housing: PA66,UL94V-0
 螺丝/Screws: M3.0, steel Zinc plated
 方块/Wire guard: Brass,Ni plated
 簧片/Clamp: Phosphor bronze,Ni plated

订购方式: HOW TO ORDER



TOLERANCES EXCEPT AS NOTED

variable range	linear dimension					fillet	chamfer	short angle sid			≡	-	□	//	⊥		
	to 6	over 6 to 30	over 30 to 120	over 120 to 480	over 480 to	all	to 6	over 6 to 10	to 10	over 10 to 50	over 50 to 120	to 10	to 5	over 5 to 30	over 30 to 120	over 120 to	
tolerance	±0.1	±0.2	±0.3	±0.5	±0.9	±0.2	±0.5	±1	1°	30'	20'	10'	0.5	0.025	0.06	0.12	0.4

单位/UNITS	mm	尺寸/SIZE	A4	比例/SCALE	第一视角/FIRST ANGLE PROJECTION	
Cixi Dibo Electronics Co.,LTD					名称/NAME	DB2EKM-7.5/7.62-XXP