

PRODUCT NO. DSHPO2TSGE1
RoHS compliant






NOTES :1.Specification:

- 1>.Operating force:10000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Electrical Life:1000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations



2. PLATING:
GOLD FLASH 1u"(min.) SOLDERTAIL,
3u" GOLD PLATING ON THE CONTACT AREA,
WITH 50u" NICKEL UNDERPLATINGOVERALL.
3. PART NUMBER DESCRIPTION :

DSHP XX I S G E I

- [包装方式: T=管装 R=Reel]
- [电键层: B=接触部 S=焊脚部 L=2u" G=接触部 S=焊脚部 3u" F=接触部 10u" 焊脚部 10u"]
- [G=键全金 S=内镀金(接触部)外镀锡(焊脚部)]
- [脚型: S脚 / J脚 / 埋脚 / A脚 / 2脚]
- [T=低推贴胶 S=低推不贴胶 L=长推]
- [产品P数: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



1	Actuator	UL94 V0	White
2	Cover	UL94 V0	Black
3	Movable	Beryllium Copper	3u" Gold
4	Terminal	Brass	1u" Gold
5	Base	UL94 V0	Black
6	Terminal Contact	Brass	3u" Gold
7	Mylar	UL94 V0	0.05mm

Number	Part Name	Material	Finished
1	Actuator	UL94 V0	White
2	Cover	UL94 V0	Black
3	Movable	Beryllium Copper	3u" Gold
4	Terminal	Brass	1u" Gold
5	Base	UL94 V0	Black
6	Terminal Contact	Brass	3u" Gold
7	Mylar	UL94 V0	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	
LINER	ANGLES	PROJECTION	
0 ± 0.25	0 ± 2'		
.00 ± 0.15	.0 ± 1'		
.000 ± 0.10	.00 ± 0.5'		
DESIGN	kathy	03/20/12	
DRAWING			
CHECK			
APPRO.			

东莞市广智实业有限公司
Dongguan Kingtek Industrial Co., Ltd.

TITLE
BY DSHP SERIES PITCH 1.27mm

PRODUCT FAMILY DSHP SERIES
PRAT NO. DSHPO2TSGE1

FILE NO. DSHPO2TSGE1-A
SIZE UNIT SCALE SHEET REV.
A4 mm Z : 1 1OF 1 A