



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS

Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Dimen Sions List

Contacts Per row	Dimensions		Contacts Per row	Dimensions	
	A	B		A	B
2	4.50	2.00	21	42.50	40.00
3	6.50	4.00	22	44.50	42.00
4	8.50	6.00	23	46.50	44.00
5	10.50	8.00	24	48.50	46.00
6	12.50	10.00	25	50.50	48.00
7	14.50	12.00	26	52.50	50.00
8	16.50	14.00	27	54.50	52.00
9	18.50	16.00	28	56.50	54.00
10	20.50	18.00	29	58.50	56.00
11	22.50	20.00	30	60.50	58.00
12	24.50	22.00	31	62.50	60.00
13	26.50	24.00	32	64.50	62.00
14	28.50	26.00	33	66.50	64.00
15	30.50	28.00	34	68.50	66.00
16	32.50	30.00	35	70.50	68.00
17	34.50	32.00	36	72.50	70.00
18	36.50	34.00	37	74.50	72.00
19	38.50	36.00	38	76.50	74.00
20	40.50	38.00	39	78.50	76.00
			40	80.50	78.00

Ordering Information

25 43 U-2 XX X W XX M N X 01

Plastic high
43=H4.3mm

No.of Pins
Per Row
01~40P

Insulator Material
Option
A=PBT
B=PA66
C=PA6T
D=PA46
E=PA9T
F=LCP

Past
W=with Post
N=w/o post

Contact Plating
G0:0.8U" Gold
G1:1U" Gold
G2:1.5U" Gold
G3:2U" Gold
G4:3U" Gold
G5:5U" Gold
G6:10U" Gold
G7:15U" Gold
S0:Gold Flash/Tin
SN:Tin

Packing
O=PE Bag
A=Tray
T=Tube
P=Tube+Cap
R=Reel+Cap
M=Reel+Mylar

code stream
01~99



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.00X4.3FH 2XNPIN W6.5 SMT
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. 2543U-2XXXWXXMNX01
UNIT: mm [inch]	APPROVED BY:	DATE : 2014-02-23	DRAW NO: HYC-1812011052
SCALE: 1:1 SIZE: A4			SHEET NO. 1 OF 1