

P/N LEGEND


A2100 H-XP XXX
① ② ③ ④

① Series No.
② Connector type: H=Housing
③ No. of circuits
④ Option code:
Blank=Color:Yellow(153C~154C)
-OR=Color:Orange(7522C)
-OR1=Color:Orange(7524C)

SPECIFICATIONS

Current Rating: 3A AC,DC
Voltage Rating: 300V AC,DC
Temperature Range: -25°C ~ +85°C
Contact Resistance: 20mΩ Max
Insulation Resistance: 100MΩ Min
Withstanding Voltage: 1000V AC/minute
Material: Nylon 66,UL94V-0

Circuit No.	Dimensions		
	A	B	C
02P	2.00	5.60	4.60
03P	4.00	7.60	6.60
04P	6.00	9.60	8.60
05P	8.00	11.60	10.60
06P	10.00	13.60	12.60
07P	12.00	15.60	14.60
08P	14.00	17.60	16.60
09P	16.00	19.60	18.60
10P	18.00	21.60	20.60
11P	20.00	23.60	22.60
12P	22.00	25.60	24.60
13P	24.00	27.60	26.60
14P	26.00	29.60	28.60
15P	28.00	31.60	30.60

				燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.					
UNIT	SCALE	SHEET	TITLE:						
mm	1 : 1	1 of 1	2.00mm PITCH HOUSING						
DRAWN BY	APPROVED BY						DRAW NO. :		REV.
董正一	董正一								
2001.02.01	2001.02.01				B3				
GENERAL TOLERANCE									
B3	EN1310080352	2013.10.08	郭本思	X. X±0.25	ANGLE±				
B2	EN1204200110	2012.04.20	陳錦展	X. XX±0.15					
REV.	DESCRIPTION	DATE	NAME	X. XXX±0.05					