



Ordering code

A3961 H-XP XXX			
①	②	③	④
① Series No.			
② Connector type: H=Housing			
③ No. of circuits			
④ Option code:			
Blank=Nylon 66,UL94V-0, Color: Natural(White)			
-RD =Nylon 66,UL94V-0, Color: Red			
Pantone color: 1785C			
-BL =Nylon 66,UL94V-0, Color: Blue			
Pantone color: 660C			
-BK =Nylon 66,UL94V-0, Color: Natural(Black)			
-PU =Nylon 66,UL94V-0, Color: Lavender			
Pantone color: 2583C			
-NF =Nylon 66,UL94V-2 NO FLAME			
Color: Natural(Beige)			

SPECIFICATIONS

Current Rating: 7A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 10mΩ Max.
 Insulation Resistance: 1000MΩ Min.
 Withstanding Voltage: 1500V AC/minute

Circuit No.	Dimensions		Circuit No.	Dimensions	
	A	B		A	B
02P	3.96	8.02	09P	31.68	35.74
03P	7.92	11.98	10P	35.64	39.70
04P	11.88	15.94	11P	39.60	43.66
05P	15.84	19.90	12P	43.56	47.62
06P	19.80	23.86	13P	47.52	51.58
07P	23.76	27.82	14P	51.48	55.54
08P	27.72	31.78	15P	55.44	59.50

 燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.					
UNIT	SCALE	SHEET	TITLE:		
mm		1 of 1	3.96mm PITCH HOUSING		
DRAWN BY	APPROVED BY				
董正一	董正一				
2001.02.01	2001.02.01				
GENERAL TOLERANCE					
B5	EN1507130001	2015.07.31	郭木恩	X.X±0.25	ANGLE±
B4	EN1304160111	2013.04.16	郭木恩	X.XX±0.15	
REV.	DESCRIPTION	DATE	NAME	X.XXX±0.05	
				DRAW NO.:	REV.
				A3961H-XP	B5