

**SPECIFICATIONS**

Rated(额定参数): 600V,25A  
 Dielectric strength(抗电强度): AC2000V/1 Minute  
 Insulation Resistance(绝缘电阻):1000MΩ Min  
 Contact Resistance(接触电阻):20mΩ Max  
 Screw Torque(扭矩): 1.2Nm (10.53lb.in)  
 Wire Range(线径):22~12AWG  
 Temp. range(操作温度): -40°C~+105°C  
 MAX Soldering(瞬时温度):+250°C,5s

Housing Material(塑件): PBT (UL94 V-0)  
 Contact(端子): Brass, 1.0t, Tin plating(黄铜镀锡)  
 Screw (螺丝): M4.0, Steel, Ni plating(钢 镀镍)

PITCH RANGE		NOMINAL DIMENSION RANGE					
IN MM		IN MM		IN MM		IN MM	
OVER	TO	OVER	TO	OVER	TO	OVER	TO
6	10	10	24	30	60	100	150
±0.10	±0.15	±0.25	±0.30	±0.30	±0.50	±0.70	±1.00





**Ordering Information**

**JL-250-121 XX B X 1**

Pitch  
121=12.10PH  
No.of pins  
2P~24P

Housing Color  
B=Black  
G=Green  
U=Blue  
R=Red  
W=White  
Y=Yellow  
O=Orange  
F=Grey

Packing  
O=Pe bog  
T=Tube  
A=Troy



REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	BEN	17.01.04	SCALE	FIT	PART NO.	TITLE:
				UNIT	SIZE				SHEET	PROJ.		
A0	2017.01.04	NEW DRAWING		X.X	±0.30	CHECK		mm	A4	1/1	JL-250-121XXBX1	12.10mm Barrier Terminal Blocks
1				X.XX	±0.20							
				X.XXX	±0.10							
				Angle	±3°	APPROVE						
				DIM	TOL							

**JIN** 深圳市锦凌电子有限公司  
 SHENZHEN JINLING ELECTRONIC CO.,LTD  
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992