


REV.	ECON. NO.	APPD.
A		

NOTES:
 Current Rating: 1.0AMP
 Contact Resistance: 20mΩ max
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C
 Contact Material: Phosphor Bronze
 Contact plating: Au Over Ni
 Insulator Material: PBT+30%GF (UL94V-0)

Ordering Information

MTFC32-XXUW

- No. of Pins
- 06P 30P
 - 08P 34P
 - 10P 40P
 - 12P 44P
 - 14P 50P
 - 16P 60P
 - 20P 68P
 - 26P 80P



X.	± 0.30	X.°	± 5°	UNITS	mm	NAME (INTENDED USE)	MINTRON CO., LTD.
X	± 0.20	X°	± 2°	MATL		PART NO. (INTENDED USE)	IDC SOCKET 1.27*1.27 WITH BUMP
XX	± 0.10	XX°	± 1°	FINISH		APPD:	SUNNY
.XXX ± 0.05	.XXX° ± 0.5°			QTY		CHKD:	USA
IDC SOCKET CONNECTOR						DR:	ZOE
							2006-11-28
						DWG NO.:	MTFC32-XXUW
						SCALE	1 / 1
						SHEET	1 / 1
						REV.	A