


78P	52.23	61.10	67.10	2.41	10.80	12.50
62P	54.84	63.50	69.32	2.41	7.92	12.50
44P	38.38	47.04	53.04	2.29	7.92	12.50
26P	24.66	33.32	39.14	2.29	7.92	12.50
15P	16.33	24.99	30.81	2.29	7.92	12.50
POS. NO.	A	B	C	D	E	F
	DIMENSION					



SPECIFICATIONS:

Current rating:3.0A AC/DC
 Voltage rating:250V AC/DC
 Contact resistance:30m ohm MAX
 Insulation resistance:5000M ohm MIN
 Withstanding voltage:1000V AC for one minute
 Operating temperature range:-40°C~+85°C

MATERIAL AND FINISH

Insulator:PBT+30%G.F<UL94V-0>
 Contact:Copper Alloy Nickel Undercoated
 Selective Gold Plated
 Finish:Metal Iron With Tin Plated

PART NO.:

Z-SUB HP * F * 0 * * * * *
 NO. OF CONTACTS ———— * F * 0 * * * * *
 B=15PIN
 D=26PIN
 F=44PIN
 D=62PIN
 H=78PIN
 LOGO
 0=NO LOGO
 2=NEXTRON
 INSULATOR COLOR
 0=BLACK
 6=BLUE
 9=WHITE
 INSULATOR MATERIAL
 0=PBT
 2=NYLON
 CONTACT PLATED:(CONTACT AREA)
 1=FULL GOLD 1u"
 2=GOLD 3u"
 3=GOLD 5u"
 5=GOLD 15u"
 6=GOLD 30u"
 MOUNTING OPTIONS
 1=RIVETED W/SHIELD ONLY
 2=RIVETED W/FRONT RIVET
 3=RIVETED W/REAR RIVET
 4=RIVETED W/NUT RIVET
 5=RIVETED W/HEX SCREW +HEX NUT
 CONTACT MATERIAL
 7=PHOSPHOR BRONZE

正凌精密工业(广东)有限公司
 内部资料请勿复印

A	NEW RELEASED	12/7'16
REV.	DESCRIPTION	DATE

UNITS mm INCH	NAME: D-SUB HDP TYPE FEMALE PCB SOLDER	 NEXTRONICS ENGINEERING CORP.	
GENERAL TOLERANCES: (UNLESS SPECIFIED)	PART NO: Z-SUBHP*F*0*****	TITLE: CUSTOMER DWG	
4 PLACE ± ** ± **	APPD: 楊海文	DWG NO: 010-0000-****	
3 PLACE ± ** ± **	CHKD: 廖小瓊	C	
2 PLACE ± 0.10 ± **	DRAWN: 陳惠枝	SCALE: SHEET: REV.:	
1 PLACE ± 0.30 ± **	2016/11/15	4/1	1/1
ANGULAR: X°±1° .X°±**			A