



Top view

Recommended P.C.B Layout

### MATERIAL



Contact Pin : Brass  
Insulation : NY6T UL94-V0

### SPECIFICATION

Current Rate : 3 AMP  
Insulation Resistance : 5000MΩMin. at DC 500V  
Contact Resistance : 20mΩMax. at DC 100mA  
Dielectric Voltage : AC 500V for one minute  
适用波峰焊制程温度: 260°C±5°C 3~5s

210-9 1- 02 G B 01  
1 2 3 4 5 6

1. 7: Green Product
- 9: Green Product High Temp
2. 1: Single row
- 2: Dual rows
3. No. of contacts per row
4. G: Gold flash
- S: Selective
5. B: Black Insulator
6. Pinrex internal code.
- 116/61/30 BULK PACK



F	修正材質, NY9T->NY6T	2018/05/23	<b>TOLERANCE</b> .0 =±.30 .00 =±.20 .000 =±.XXX .0000=±. ANG.=±3'		OLD PART NO.			TITLE			
E	增加描述	2013/07/18			DRAWER 杨海琴		CHECK 李劍		PIN HEADER 2.54*2.54mm STRAIGHT TYPE, SINGLE ROW		
D	增加描述	2013/02/26			UNITS : mm				PINREX 频锐科技股份有限公司		
C	REVISE HOUSING SIZE	2011/08/02			SCALE NONE	SIZE A4	SHEET 1 OF 1	REV. F	APP'D 李劍	PINREX TECHNOLOGY CORP.	
B	REVISE DIMENSIONS	2007/10/08						NEW PART NO. 210-91-02GB01			DRAW NO. 210-91-02GB01(F版)
REV.	DESCRIPTION	DATE									