

Recommended P.C.Board layout

MATERIAL



Insulator : NYLON 66 + 30% Glass fiber
 Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
 Dielectric voltage : 1000V AC for one minute
 Insulation Resistance : 1000MΩMin
 Contact Resistance : 20mΩMax

753-8 1-06 8 W 00
 1 2 3 4 5

- 1. 8: Green Product
- 2. No. of contacts per row
- 3. G: Gold flash
 S: Selective
 T: Tin plated
 8: 8u"Gold plated
 5: Matte Gold plated
- 4. S: Crystal insulator
 W: White Insulator
- 5. Pinrex internal code.

				TOLERANCE				OLD PART NO.		TITLE		 频锐科技股份有限公司	
				.0 =±.30		UNITS : mm		DRAWER 廖小芳		2.5mm HEADER DIP TYPE		PINREX TECHNOLOGY CORP.	
				.00 =±.20		SCALE NONE		SHEET 1 OF 1		NEW PART NO.		DRAW NO.	
A		RELEASE		2015/01/26		SIZE A4		REV. A		753-81-068W00		753-81-068W00	
REV.		DESCRIPTION		DATE									