


REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



- NOTES:
- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE: 3.0 OHMMAX.
 - INSULATION RESISTANCE: 5.0M OHMMIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPENS/SHORT, MISWIRING AND INTERMITTENT FAILURES
 - MATERIAL:
 - SEE TABLE
 - ALL COMPONENTS ARE ROHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	端子	高仿I-PEX, 1代端子, 镀金	1
②	接头	SMA母头母针, 分体, 11牙, 镀金	1
①	同轴线	Rg178棕色线, OD:1.80mm	AS

金航标电子有限公司

ALL DIMENSION ARE IN MM		DRAWN	DATE	I-PEX 178 TO SMA /F L=180MM	
		James	2019-06-01	SIZE	Number
COMPUTER GENERATED IN SOLIDWORKS		CHKD.	Frank	2019-06-01	B
DO NOT SCALE THIS DRAWING		Appd.	Scott	2019-06-01	REV
PROJECTION		GENERAL TOLERANCE FOR ANGLES		A	
		$\pm 1^\circ$ ± 0.3 ± 0.25 ± 0.150		SCALE: Free	
CUSTOMER P.N.:		TYPE		SHEET 1 OF 1	

4 3 2 1