#### EMC Components

### **Common mode filters** Automotive signal line (for power train/safety) **ACT** series



#### **FEATURES**

AEC-Q200

- Compatible with an operating temperature range of -40 to +150°C, so can be used for vehicle devices requiring compatibility with high temperatures.
- O When mounting, the terminal and winding tape splicing part do not fuse.
- O Which uses our unique technology, is a product that can achieve DCR<2Ω@125deg.C by reducing the DC resistance while maintaining a high L-value of 100uH.
- Operating temperature range: -40 to +150°C

Compliant with AEC-Q200


ACT45R type

#### APPLICATION

FlexRay system.

O Application guides: Automotive (xEV), Car Infotainment

#### PART NUMBER CONSTRUCTION



#### CHARACTERISTICS SPECIFICATION TABLE

Common mode		Common mode inductance	Stray inductance	DC resistance	Rated current	Insulation resistance	Rated voltage	Part No.
[10MHz]		[100kHz]	[100kHz]				U U	
<b>(</b> Ω <b>)min.</b>	<b>(</b> Ω <b>)typ.</b>	(µH)+50/–30%	(µH)typ.	<b>(</b> Ω <b>)max.</b>	(A)max.	<b>(M</b> Ω)min.	(V)max.	
2200	5500	100	0.2	1.5	0.2	10	50	ACT45R-101-2P-TL001

#### Measurement equipment

Measurement item	Product No.	Manufacturer
Common mode impedance	4991A	Keysight Technologies
Common mode inductance	4294A	Keysight Technologies
DC resistance	4338A	Keysight Technologies
Insulation resistance	4339A	Keysight Technologies


\* Equivalent measurement equipment may be used.





# ACT45R type

#### ■ IMPEDANCE VS. FREQUENCY CHARACTERISTICS




Product No.	Manufacturer		
4991A	Keysight Technologies		

\* Equivalent measurement equipment may be used.


# ACT45R type

#### SHAPE & DIMENSIONS




Dimensions in mm

#### RECOMMENDED LAND PATTERN




Dimensions in mm

#### **CIRCUIT DIAGRAM**




No polarity

### RECOMMENDED REFLOW PROFILE





#### PACKAGING STYLE




Dimensions in mm

#### **TAPE DIMENSIONS**







Dimensions in mm

#### **PACKAGE QUANTITY**

Package quantity 2,500 pcs/reel

#### TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating	Storage	Individual
temperature range	temperature range*	weight
–40 to +150 °C	–40 to +150 °C	0.14 g

The storage temperature range is for after the assembly.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (3/4)

## **REMINDERS FOR USING THESE PRODUCTS**

Before using these products, be sure to request the delivery specifications.

## SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

<u> </u>	MINDERS
<ul> <li>The storage period is less than 12 months. Be sure to follow the less).</li> <li>If the storage period elapses, the soldering of the terminal elect</li> </ul>	storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH o
O Do not use or store in locations where there are conditions such	i as gas corrosion (salt, acid, alkali, etc.).
<ul> <li>Before soldering, be sure to preheat components.</li> <li>The preheating temperature should be set so that the tempera does not exceed 150°C.</li> </ul>	ature difference between the solder temperature and chip temperature
<ul> <li>Soldering corrections after mounting should be within the range If overheated, a short circuit, performance deterioration, or lifes</li> </ul>	-
When embedding a printed circuit board where a chip is mount the overall distortion of the printed circuit board and partial distortion	ted to a set, be sure that residual stress is not given to the chip due to ortion such as at screw tightening portions.
<ul> <li>Self heating (temperature increase) occurs when the power is design.</li> </ul>	s turned ON, so the tolerance should be sufficient for the set therma
<ul> <li>Carefully lay out the coil for the circuit board design of the non-n A malfunction may occur due to magnetic interference.</li> </ul>	nagnetic shield type.
O Use a wrist band to discharge static electricity in your body through	ugh the grounding wire.
$\bigcirc$ Do not expose the products to magnets or magnetic fields.	
$\bigcirc$ Do not use for a purpose outside of the contents regulated in the	e delivery specifications.
ment, home appliances, amusement equipment, computer equipment, industrial robots) under a normal operation and use cond The products are not designed or warranted to meet the required ity require a more stringent level of safety or reliability, or whose person or property.	neral electronic equipment (AV equipment, telecommunications equip- uipment, personal equipment, office equipment, measurement equip- ition. ments of the applications listed below, whose performance and/or qual- e failure, malfunction or trouble could cause serious damage to society or if you have special requirements exceeding the range or conditions
<ul> <li>(1) Aerospace/aviation equipment</li> <li>(2) Transportation equipment (electric trains, ships, etc.)</li> <li>(3) Medical equipment</li> <li>(4) Power-generation control equipment</li> <li>(5) Atomic energy-related equipment</li> <li>(6) Seabed equipment</li> <li>(7) Transportation control equipment</li> </ul> When designing your equipment even for general-purpose applicate tection circuit/device or providing backup circuits in your equipment	<ul> <li>(8) Public information-processing equipment</li> <li>(9) Military equipment</li> <li>(10) Electric heating apparatus, burning equipment</li> <li>(11) Disaster prevention/crime prevention equipment</li> <li>(12) Safety equipment</li> <li>(13) Other applications that are not considered general-purpose applications</li> </ul>