		4				3						2		1		
	THIS DRAWING IS U	THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION SEP ,2005.										LOC DIST	REVISIONS			
	C COPYRIGHT 2005 By -											J / PT		DESCRIPTION	DATE DWN APVD	-
	NOTICE: THIS CO	MMUNICATION IN	CLUDES TE CONNECTIVI	TY CONF	IDENTIAL OR F	ROPRIE	TARY IN	FORMA	TION TH	AT MAY	ALSO BE	LEGALLY PRIVILEGED.	F8	p	4MAR19 T.ZH S.L	1
_																1
D	AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	6.28	-	0.5	10.05	_	-	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 2)	WITHOUT FLANGE TYPE (SEE SHEET 8)	1747981–3 🕞	1 D
D C	AVAILABLE	WITHOUT P/N	Au 0.76um	16.3	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	1-1747981-9	
	AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	6.28	-	0.5	10.55	-	_	1.1	1.1	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 2)	WITHOUT FLÂNGE TYPE (SEE SHEET 6)	9-1747981-2]
	AVAILABLE	WITH P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	- 1	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITH BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	9-1747981-1	
	AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	16.3	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	8-1747981-2 2-1747981-5	[
	AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	- 1	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	CLEAR TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	8-1747981-1	1
	AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	-	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITH BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	3-1747981-1	
	NOT AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	16.3	#4-40 UNC	0.5	10.55	12.75	10.08	2.2	1.8	WITH BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	2-1747981-4	
	AVAILABLE	WITHOUT P/N	Au 0.76um MIN	16.3	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	2-1747981-3]
С	NOT AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	- 1	#4-40 UNC	0.5	10.05	12.75	10.08	2.2	1.8	WITHOUT BOSS	HARDTRAY PACKING (-)	WITH FLANGE TYPE (SEE SHEET 7)	2-1747981-2] c
	AVAILABLE	WITHOUT P/N	Au 0.76um MIN	-	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	2-1747981-1	1
	AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	-	M3 x 0.5	1.0	10.55	12.75	10.08	1.5	1.5	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 4)	WITH FLANGE TYPE (SEE SHEET 7)	1-1747981-8	
	AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	16.3	M3 x 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3)	WITH FLANGE TYPE (SEE SHEET 7)	1-1747981-7	
_	AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	-	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	SOFT TRAY PACKING (SEE SHEET 5)	WITH FLANGE TYPE (SEE SHEET 7)	1-1747981-6	5
	AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN Au 0.1um MIN	16.3	M3 × 0.5	0.5	10.05	10.95	7.98	1.5	1.5	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 3) SOFT TRAY PACKING	WITH FLANGE TYPE (SEE SHEET 7) WITH FLANGE TYPE	1-1747981-5	
	AVAILABLE	WITHOUT P/N	OVER PdNi 0.2um MIN Au 0.1um MIN	-	M3 × 0.5	1.0	10.55	12.75	10.08	2.2	1.8	WITHOUT BOSS	(SEE SHEET 4) SOFT TRAY PACKING	(SEE SHEET 7) WITH FLANGE TYPE	1-1747981-4	
В	AVAILABLE	WITHOUT P/N	OVER PdNi 0.2um MIN		#4-40 UNC M3 x 0.5	0.5 0.5	10.05 10.05	12.75 10.95	10.08 7.98	2.2 1.5	1.8 1.5	WITHOUT BOSS	(SEE SHEET 4) SOFT_TRAY_PACKING	(SEE SHEET 7) WITH FLANGE TYPE	1-1747981-3	E
	AVAILABLE	WITHOUT P/N	Au 0.1um MIN	_	M3 x 0.5	0.5	10.05	10.95	7.98	2.2	1.8	WITHOUT BOSS	(SEE SHEET 4) SOFT TRAY PACKING	(SEE SHEET 7) WITH FLANGE TYPE	1-1747981-1	1
	AVAILABLE	WITHOUT P/N	OVER PdNi 0.2um MIN Au 0.1um MIN OVER PdNi 0.2um MIN	6.28	-	0.5	10.05	_	-	1.5	1.5	WITHOUT BOSS	(SEE SHEET 4) EMBOSS PACKING (SEE SHEET 2)	(SEE SHEET 7) WITHOUT FLANGE TYPE (SEE SHEET 6)	1747981-2	1
	AVAILABLE	WITHOUT P/N	Au 0.1um MIN OVER PdNi 0.2um MIN	6.28	-	0.5	10.05	_	-	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 2)	WITHOUT FLANGE TYPE (SEE SHEET 6)	1747981-1	1
	AVAILABLE	WITHOUT P/N	Au 0.76um MIN CONTACT ALEA	6.28	– Screw size	0.5	10.05	-	_	2.2	1.8	WITHOUT BOSS	EMBOSS PACKING (SEE SHEET 2)	WITHOUT FLANGE TYPE (SEE SHEET 6)	3-1747981-2	
	TOOL STATUS		PLATING SPEC J		DIM G 🕭								PACKING 155EP2005	CONNECTOR TYPE	PART NUMBER	-
	1 CONTACT COPLANALITY IS 0.1 MAXIMUM. A REFER TO THE TABLE FOR BO THIS DIMENSION MEANS CENTER OF THE POCKET. SCREW SIZE SS. FINISH SCREW SIZE SS.								THIS DRAWING IS A CONTROLLED DOCUMENT. UNIX 155EP2005 CHK 155EP2005 TKIMURA 155EP2005 T.KIMURA TE Connectivity							
А	CONTACT: CONTACT AREA J: SEE TABLE 2							D	mm	0	OTHERWI: PLC	± 0.2	15SEP2005 NAME	HDMI 19 POS		
									\bigoplus	1 2 3	1 PLC 2 PLC 3 PLC	0.2 APPLICATION SP	B180-1 C SIZE CACE CODE DRAWING NO A 3 00779 C-1747981			
								MATERIAL		A	PLC NGLES TINISH	± 0.2 ± - WEIGHT			RESTRICTED TO	1
									CUSTOMER DRAWING SCALE NTS SHEE					1 of 9 F8		















