



| REV. | DESCRIPTION | APPD | DATE |
|------|-------------|------|------|
| | | | |

NOTES:

- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94V_0,COLOR:BLACK.
CONTACT: COPPER ALLOYS.
COVER: COPPER ALLOYS OR STEEL.
- PLATING:
UNDERPLATE: NICKEL.
CONTACT AREA: GOLD OVER NICKEL.
SOLDER AREA: TIN OVER NICKEL.
- MULTIMEDIA CARD COMPATIBLE



| PIN NO. | NAME | YTYPE | DESCRIPTION |
|---------|----------|--------|----------------------------|
| 1 | DATE2 | I/O/PP | DATE LINE(BIT2) |
| 2 | CD/DATE3 | I/O/PP | CARD DETECT DATE LIN(BIT3) |
| 3 | CMD | PP | COMMAND RESPONSE |
| 4 | VDD | S | SUPPLY VOLTAGE |
| 5 | CLK | I | CLOCK |
| 6 | VSS | S | SUPPLY VOLTAGE GROUND |
| 7 | DATE0 | I/O/PP | DATE LINE(BIT0) |
| 8 | DATE1 | I/O/PP | DATE LINE(DIT1) |



| PART NO: | | MATERIAL: | |
|--|---|--------------------------------------|---------------|
| LOT NO: | FINISH: | DR: | DWG NO: |
| UNIT: MM | COLOR: | CHK: | TFW09-HRJ-68A |
| SIZE: A4 | TITLE: | APP: | SCALE: 1:1 |
| TOLERANCES: X.X=±0.35 X.XX=±0.25 X.XXX=±0.15 | GENERAL ANGLE: X.X=±3.0° X.XX=±2.0° | DR: | REV: B/1 |
| 深圳市台华达科技有限公司 SHENZHENSHI THD ELECTRONICS CO.,LTD. | | TITLE: T-FLASH 外焊卡座 SHEET: 1 OF 3 | |