


REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD

1 2 3 4 5 6 7 8


A
B
C
D
E
F

A
B
C
D
E
F



Electrical
 Current Rating: 1A AC(rms)/DC
 Voltage Rating: 30V AC(rms)/DC
 Contact Resistance: 20 mΩ Max
 Insulation Resistance: 1000 MΩ MIN
 Withstanding Voltage: 600V AC r.m.s
 Temperature Range—Operating: -40°C~+85°C

Material and Plating
 Housing: LCP(UL 94V-0)
 Contact Pin: Phosphor Bronze
 Plating: Selective gold in contact area, Tin on tail.




Recommended P.C.Board Layout

Ordering Informaion

FUS 1 19 — F S B K6 X
 1 2 3 4 5 6 7 8

1	Category	2	Series Number	3	Distinction No.	4	Type
	FUS-USB		1-Mini USB		19		F-Female
5	Assembly Layout	6	Entry Angle	7	Color-Resin	8	Packaging
	S-SMT		B-90° Angle		K6-Black		L-Tube M-Reel

THIRD ANGLE PROJECTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY	DATE	PART NO.	ITEM NO.	 Leader Of Industry
	X.±.012(0.30)	X.±5'	FRANK	17JUL/13	FUS119-FSBK6X	FUS119	
DESIGN UNITS	X.X±.008(0.20)	X.±2'	CHECKED BY	DATE	TITLE		REV 0
Inch (metric)	X.XX±.006(0.15)	.XX±1'	CHERRY	17/JUL/13	Mini USB		
SCALE	X.XXX±.004(0.10)	.XXX±0.5'	DRAWN BY	DATE	5Circuits 90°Angle Female(SMT)		SHEET NO. 1/1
5:1			JACOB	17/JUL/13	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

1 2 3 4 5 6 7 8