



REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD
1	▲	Structure change	12/SEP/19	KATE	CHERRY

SPECIFICATIONS

Electrical  
 Current Rating: 1.5A AC(rms)/DC  
 Voltage Rating: 30V AC(rms)/DC  
 Contact Resistance: 30 mΩ Max  
 Withstanding Voltage: 500V AC r.m.s  
 Insulation Resistance: 1000 MΩ Min  
 Temperature Range-Operating: -40°C~+85°C

Material  
 Housing: LCP (UL 94V-0) Blue  
 Terminal: Phosphor Bronze  
 Shell: SPCC

Plating  
 Terminal: Gold in contact area, tin on tail  
 Shell: Nickel Plated



Recommended P.C.Board Layout

 THIRD ANGLE PROJECTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 13/MAR/17	PART NO. FUS322-MSBU1K	ITEM NO. FUS322	 Leader Of Industry
	DESIGN UNITS Inch (metric)	X.±.012(0.30)	X.±5°	CHECKED BY CHERRY	DATE 13/MAR/17	TITLE USB A-type 9Circuits 90°Angle Male(SMT)(3.0)	
SCALE 5:1	SIZE A4	X.XX±.006(0.15)	.XX±1°	DRAWN BY KATE	DATE 13/MAR/17	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	REV 1 SHEET NO. 1/1