



SWITCH CONNECTOR

| | | | | | | | | | | | | | |
|---|-------------|------|---------|----------|--|------------------------|------|---------------------------------------|--|------|--------|------------|-------------------------------|
| | | | | | | ANGLAR | ±5° | DSND | | DATE | | SCALE: N/A | MODEL TYPE: 3.5 PHONE JACK |
| △X | | | | | | L ≤ 4 | ±0.2 | DWN | | DATE | | VIEW: | PART NO.: |
| △X | | | | | | 4 < L ≤ 16 | ±0.3 | CHKD | | DATE | | UNIT: mm | |
| △X | | | | | | 16 < L ≤ 63 | ±0.4 | APPD | | DATE | | SIZE: A4 | DWG NO.: |
| MARK | DESCRIPTION | DATE | REVISED | APPROVED | | L > 63 | ±0.5 | | | | | | PJ-3254B |
| REVISIONS | | | | | | UNSPECIFIED TOLERANCES | | XKB INDUSTRIAL PRECISION CO., LIMITED | | | WEIGHT | SHEET | REVISION |
| www.xk-dg.cn www.helloxkb.com www.helloxkb.cn | | | | | | | | | | | 1.0g | 1/1 | A0 |