

尼龙电缆固定头
Nylon Cable Glands

CE ROHS IP68



产品材质：A.C.E.F部位采用尼龙制成，D部位采用丁腈橡胶制成。

螺纹规格：公制、德制、英制。

工作温度：静态：-40℃到+100℃,短时可达+120℃，动态：-20℃到+80℃,短时可达+100℃。

颜色：黑色，灰色(特殊颜色可定做)。

防护等级：在规定的卡口范围内，并使用O形密封圈旋紧迫紧头，达到IP65

产品特性：夹紧爪与密封件的特殊之设计，配合迫紧头装配省时便利，夹紧电缆范围大，抗拉力特强，可防水，防尘，防酸，防盐，耐酸碱，酒精，油，脂及一般溶剂。

使用方法：塑料电缆防水接头是电缆的配套产品，接头可将电缆锁紧，另一端可接入设备箱体上，也可以根据选用螺纹接入进出口为内螺纹的电动设备上。

Product material: Location A.C.E and F made Of PA;Location D made Of chemigum

Specification of th read: MetriC PG and G


Working temperature: Static: -40°C~+100°C,instantaneously can be+120°C: Dynamic: -20°C~+80°C instantaneously can be+100°C:

Color: Black and gray(special colors customizable)

Protection classification: Within the specified clamp range,use O-shaped sealing ring and screwtightthe pressing fastener,reaching Ip65.

Property: the special designs for clamping jaw and sealants fitted with the pressing fastener can save both time and energy,promising a wide scope for cable clamping and extremely great stretching resistance.It iS water resistant,dust resistant and inactive with salts,acids,alkalis,oils and greases as well as general dissolvent

How to use: waterp roof nylon cable glands are the fittings for cables The ioints can lock the cables tight The other end of the Joint can be either connected with the housing of equipments or connected with electric equipment with inner threaded access hole as per the thread selected





德制螺纹 PG Thread

型号 Item NO.	德制螺纹 PG	电缆范围 cable range (mm)	D1	D2	L1	L2	L3	B1	包装数 (只)
PG-07	PG7	3.5-6.5	12.5	8.1	10.4	14.5	10.5	6.4	100
PG-09	PG9	4-8	15.2	12.2	9.9	15.8	17.2	8.6	100
PG-11	PG11	5-10	18.2	14.6	10.6	15.5	17.5	10.7	100
PG-13.5	PG13.5	6-12	20.2	16.2	10.3	17.8	17.9	13.3	100
PG-16	PG16	10-14	22.2	18.3	11.2	18.5	20.5	14.3	100
PG-19	PG19	12-15	24.7	20.5	11.4	18.6	21.8	15.5	100
PG-21	PG21	13-18	28.5	21.8	11.6	18.7	23.1	16.7	50
PG-24	PG24	15-22	29.8	25.0	12.1	19.3	24.1	19.2	50
PG-25	PG25	17-23	29.8	25.0	12.1	19.3	24.1	19.2	50
PG-29	PG29	18-25	37	29.8	12.4	22.6	24.8	24.8	50
PG-36	PG36	22-32	47	37.1	12.6	25.1	26.1	30.7	20
PG-42	PG42	30-38	54	43.3	17.3	25.9	30.5	35.6	20
PG-48	PG48	34-44	59.3	48.2	20.9	28.1	31.5	41.4	20
PG-63	PG63	42-54	71.0	63.5	27.5	31.5	43.5	55.0	10

公制螺纹 Metric Thread

型号 Item NO.	公制螺纹 METRIC	电缆范围 cable range (mm)	D1	D2	L1	L2	L3	B1	包装数 (只)
M12	M12 × 1.5	3.5-6	11.8	9	10.4	14.5	14	6.4	100
M16	M16 × 1.5	4-8	15.6	12.2	9.9	13	16	8.6	100
M18	M18 × 1.5	5-10	17.8	14.6	10.6	15.5	17.5	10.7	100
M20	M20 × 1.5	6-12	19.6	16.2	10.3	17.8	17.9	13.3	100
M22	M22 × 1.5	10-14	21.8	18.3	11.2	18.5	20.5	14.3	100
M24	M24 × 1.5	12-15	24.7	20.5	11.4	18.6	21.8	15.5	100
M25	M25 × 1.5	13-18	24.5	21.8	11.6	18.7	23.1	16.7	50
M30	M30 × 1.5	15-22	30.0	25.0	12.1	19.3	24.1	19.2	50
M32	M32 × 1.5	17-23	32.0	25.0	12.1	19.3	24.1	19.2	50
M36	M36 × 1.5	18-25	36.0	29.8	12.4	22.6	24.8	24.8	50
M40	M40 × 1.5	22-32	40.0	37.1	12.6	25.1	26.1	30.7	50
M50	M50 × 1.5	30-38	50.0	43.3	17.3	25.9	30.5	35.6	20
M63	M63 × 1.5	34-44	63.0	48.2	20.9	28.1	31.5	41.4	20
M71	M71 × 1.5	42-54	71.0	63.5	27.5	31.5	43.5	55.0	10

英制 G thread

型号 Item NO.	公制螺纹 METRIC	电缆范围 cable range (mm)	D1	D2	L1	L2	L3	B1	包装数 (只)
G1/2"	G1/2"	6-12	20.2	16.2	10.3	17.8	17.9	13.3	100
G3/4"	G3/4"	13-18	26.9	21.8	11.6	18.7	23.1	16.7	100
G1"	G1"	15-22	33.2	25.0	12.1	19.3	24.1	19.2	50
G1 1/4"	G1 1/4"	18-25	41.9	29.8	12.4	22.6	24.8	24.8	50
G1 1/2"	G1 1/2"	22-32	47.8	37.1	12.6	25.1	26.1	30.7	50
G2"	G2"	34-44	59.6	48.2	20.9	28.1	31.5	41.4	20