

Si823x Data Sheet

0.5 and 4.0 Amp ISOdrivers (2.5 and 5 kV_{RMS})

The Si823x isolated driver family combines two independent, isolated drivers into a single package. The Si8230/1/3/4 are high-side/low-side drivers, while the Si8232/5/7/8 are dual drivers. Versions with peak output currents of 0.5 A (Si8230/1/2/7) and 4.0 A (Si8233/4/5/8) are available. All drivers operate with a maximum supply voltage of 24 V.

The Si823x drivers utilize Silicon Labs' proprietary silicon isolation technology, which provides up to 5 kV_{RMS} withstand voltage per UL1577 and fast 45 ns propagation times. Driver outputs can be grounded to the same or separate grounds or connected to a positive or negative voltage. The TTL level compatible inputs with >400 mV hysteresis are available in individual control input (Si8230/2/3/5/7/8) or PWM input (Si8231/4) configurations. High integration, low propagation delay, small installed size, flexibility, and cost-effectiveness make the Si823x family ideal for a wide range of isolated MOSFET/IGBT gate drive applications.

Automotive Grade is available for certain part numbers. These products are built using automotive-specific flows at all steps in the manufacturing process to ensure the robustness and low defectivity required for automotive applications.

Industrial Applications

- · Power delivery systems
- · Motor control systems
- · Isolated dc-dc power supplies
- · Lighting control systems
- · Plasma displays
- · Solar and industrial inverters

Safety Regulatory Approvals

- UL 1577 recognized
 - Up to 5000 V_{RMS} for 1 minute
- CSA component notice 5A approval
 - IEC 60950-1, 62368-1, 60601-1 (reinforced insulation)
- · VDE certification conformity
 - VDE 0884-10
 - EN60950-1 (reinforced insulation)
- · CQC certification approval
 - GB4943.1

Automotive Applications

- On-board chargers
- · Battery management systems
- Charging stations
- · Traction inverters
- Hybrid Electric Vehicles
- · Battery Electric Vehicles

KEY FEATURES

- Two completely isolated drivers in one package
 - Up to 5 kV_{RMS} input-to-output isolation
 - Up to 1500 V_{DC} peak driver-to-driver differential voltage
- HS/LS and dual driver versions
- Up to 8 MHz switching frequency
- 0.5 A peak output (Si8230/1/2/7)
- 4.0 A peak output (Si8233/4/5/8)
- · High electromagnetic immunity
- · RoHS-compliant packages:
- SOIC-14/16 wide body
- SOIC-16 narrow body
- LGA-14
- QFN-14 (pin to pin compatible with LGA-14 packages)
- AEC-Q100 qualification
- Automotive-grade OPNs available
 - AIAG compliant PPAP documentation support
 - · IMDS and CAMDS listing support

1. Ordering Guide

Industrial and Automotive Grade OPNs

Industrial-grade devices (part numbers having an "-I" in their suffix) are built using well-controlled, high-quality manufacturing flows to ensure robustness and reliability. Qualifications are compliant with JEDEC, and defect reduction methodologies are used throughout definition, design, evaluation, qualification, and mass production steps.

Automotive-grade devices (part numbers having an "-A" in their suffix) are built using automotive-specific flows at all steps in the manufacturing process to ensure robustness and low defectivity. These devices are supported with AIAG-compliant Production Part Approval Process (PPAP) documentation, and feature International Material Data System (IMDS) and China Automotive Material Data System (CAMDS) listing. Qualifications are compliant with AEC-Q100, and a zero-defect methodology is maintained throughout definition, design, evaluation, qualification, and mass production steps.

Ordering Part Number (OPN)	Automotive OPN ^{5,6}	Inputs	Configuration	Peak Current	UVLO Voltage	lsolation Rating	Package Type			
Wide Body (WB) Packag	Wide Body (WB) Package Options									
Si8230BB-D-IS	Si8230BB-AS	VIA, VIB	High Side/ Low Side							
Si8231BB-D-IS	Si8231BB-AS	PWM	High Side/ Low Side	0.5 A	8 V					
Si8232BB-D-IS	Si8232BB-AS	VIA,VIB	Dual Driver							
Si8234CB-D-IS	Si8234CB-AS	PWM	High Side/ Low Side		10 V	2.5 kVrms	SOIC-16 Wide Body			
Si8233BB-D-IS	Si8233BB-AS	VIA,VIB	High Side/ Low Side	4.0 A	8 V					
Si8234BB-D-IS	Si8234BB-AS	PWM	High Side/ Low Side							
Si8235BB-D-IS	Si8235BB-AS	VIA,VIB	Dual Driver							
Si8230AB-D-IS	Si8230AB-AS	VIA, VIB	High Side/							
Si8231AB-D-IS	Si8231AB-AS	PWM	Low Side	0.5 A	5 V		SOIC-16 Wide Body			
Si8232AB-D-IS	Si8232AB-AS	VIA,VIB	Dual Driver			2.5 kVrms				
Si8233AB-D-IS	Si8233AB-AS	VIA,VIB	High Side/			2.5 KVIIIIS				
Si8234AB-D-IS	Si8234AB-AS	PWM	Low Side	4.0 A	5 V					
Si8235AB-D-IS	Si8235AB-AS	VIA,VIB	Dual Driver							
Narrow Body (NB) Pack	age Options					1				
Si8230BB-D-IS1	Si8230BB-AS1	AS1 VIA,VIB High Side/ Low Side								
Si8231BB-D-IS1	Si8231BB-AS1	PWM	High Side/ Low Side	0.5 A	8 V	2.5 kVrms	SOIC-16 Narrow Body			
Si8232BB-D-IS1	Si8232BB-AS1	VIA,VIB	Dual Driver							

Table 1.1. Si823x Ordering Guide 1, 2, 4

Ordering Part Number (OPN)	Automotive OPN ^{5,6}	Inputs	Configuration	Peak Current	UVLO Voltage	Isolation Rating	Package Type
Si8233BB-D-IS1	Si8233BB-AS1	VIA,VIB	High Side/ Low Side				
Si8234BB-D-IS1	Si8234BB-AS1	PWM	High Side/ Low Side	4.0 A	8 V	2.5 kVrms	SOIC-16 Narrow Body
Si8235BB-D-IS1	Si8235BB-AS1	VIA,VIB	Dual Driver				
Si8235BA-D-IS1	Si8235BA-AS1	VIA,VIB	Dual Driver			1.0 kVrms	
Si8230AB-D-IS1	Si8230AB-AS1	VIA,VIB	High Side/				
Si8231AB-D-IS1	Si8231AB-AS1	PWM	Low Side	0.5 A	5 V		
Si8232AB-D-IS1	Si8232AB-AS1	VIA,VIB	Dual Driver				SOIC-16
Si8233AB-D-IS1	Si8233AB-AS1	VIA,VIB	High Side/			2.5 kVrms	Narrow Body
Si8234AB-D-IS1	Si8234AB-AS1	PWM	Low Side	4.0 A	5 V		
Si8235AB-D-IS1	Si8235AB-AS1	VIA,VIB	Dual Driver				
Si8230BC-D-IS1	Si8230BC-AS1	VIA,VIB	High Side/ Low Side				
Si8231BC-D-IS1	Si8231BC-AS1	PWM	High Side/ Low Side	0.5 A	8 V 3	3.75 kVrms	SOIC-16 Narrow Body
Si8232BC-D-IS1	Si8232BC-AS1	VIA,VIB	Dual Driver				
Si8233BC-D-IS1	Si8233BC-AS1	VIA,VIB	High Side/ Low Side				SOIC-16 Narrow Body
Si8234BC-D-IS1	Si8234BC-AS1	PWM	High Side/ Low Side	4.0 A	8 V	3.75 kVrms	
Si8235BC-D-IS1	Si8235BC-AS1	VIA,VIB	Dual Driver				
Si8235BA-D-IS1	Si8235BA-AS1	VIA,VIB	Dual Driver			1.0 kVrms	
Si8230AC-D-IS1	Si8230AC-AS1	VIA,VIB	High Side/				
Si8231AC-D-IS1	Si8231AC-AS1	PWM	Low Side	0.5 A	5 V		
Si8232AC-D-IS1	Si8232AC-AS1	VIA,VIB	Dual Driver			0.75 1) (SOIC-16
Si8233AC-D-IS1	Si8233AC-AS1	VIA,VIB	High Side/			- 3.75 kVrms	Narrow Body
Si8234AC-D-IS1	Si8234AC-AS1	PWM	Low Side	4.0 A	5 V		
Si8235AC-D-IS1	Si8235AC-AS1	VIA,VIB	Dual Driver				
GA Package Options		-			1		
Si8233CB-D-IM	Si8233CB-AM				10 V		
Si8233BB-D-IM	Si8233BB-AM	VIA,VIB			8 V	1	
Si8233AB-D-IM	Si8233AB-AM		High Side/ Low Side		5 V	1	
Si8234BB-D-IM	Si8234BB-AM			4.0 A	8 V	2.5 kVrms	LGA-14 5x5 m
Si8234AB-D-IM	Si8234AB-AM	- PWM			5 V	-	
Si8235BB-D-IM	Si8235BB-AM		Du I D I		8 V	1	
Si8235AB-D-IM	Si8235AB-AM	- VIA,VIB	Dual Driver		5 V	1	

Ordering Part Number (OPN)	Automotive OPN ^{5,6}	Inputs	Configuration	Peak Current	UVLO Voltage	Isolation Rating	Package Type	
Si8233AB-D-IM1	Si8233AB-AM1	VIA,VIB			5 V			
Si8233BB-D-IM1	Si8233BB-AM1		High Side/		8 V			
Si8234AB-D-IM1	Si8234AB-AM1	- PWM	Low Side	4.0 A	5 V	2.5 kVrms	QFN-14	
Si8234BB-D-IM1	Si8234BB-AM1			4.0 A	8 V	2.5 KVIIIIS	QFN-14	
Si8235AB-D-IM1	Si8235AB-AM1	- VIA,VIB	Dual Driver		5 V			
Si8235BB-D-IM1	Si8235BB-AM1		Dual Driver		8 V			
5 kV Ordering Options								
Si8230BD-D-IS	Si8230BD-AS	VIA, VIB	High Side/ Low Side					
Si8231BD-D-IS	Si8231BD-AS	PWM	High Side/ Low Side	0.5 A				
Si8232BD-D-IS	Si8232BD-AS	VIA, VIB	Dual Driver		8 V	5.0 kVrms	SOIC-16	
Si8233BD-D-IS	Si8233BD-AS	VIA, VIB	High Side/ Low Side			5.0 KVIIIIS	Wide Body	
Si8234BD-D-IS	Si8234BD-AS	PWM	High Side/ Low Side	4.0 A				
Si8235BD-D-IS	Si8235BD-AS	VIA, VIB	Dual Driver	-				
Si8230AD-D-IS	Si8230AD-AS	VIA, VIB	High Side/					
Si8231AD-D-IS	Si8231AD-AS	PWM	Low Side	0.5 A	5 V			
Si8232AD-D-IS	Si8232AD-AS	VIA, VIB	Dual Driver			-)/	SOIC-16 Wide Body	
Si8233AD-D-IS	Si8233AD-AS	VIA, VIB	High Side/					
Si8234AD-D-IS	Si8234AD-AS	PWM	Low Side	4.0 A	5 V			
Si8235AD-D-IS	Si8235AD-AS	VIA, VIB	Dual Driver	-	5 V	5.0 kVrms		
Si8230AD-D-IS3	Si8230AD-AS3	VIA, VIB		0 5 4		5.0 KVIIIIS	SOIC-14 Wide Body	
Si8230BD-D-IS3	Si8230BD-AS3	VIA, VIB	High Side/	0.5 A	8 V	-		
Si8233AD-D-IS3	Si8233AD-AS3	VIA, VIB	Low Side		5 V			
Si8233BD-D-IS3	Si8233BD-AS3	VIA, VIB		4.0 A	8 V		with increased creepage	
Si8235AD-D-IS3	Si8235AD-AS3	VIA, VIB	Dual Driver	4.0 A	5 V		oloopugo	
Si8235BD-D-IS3	Si8235BD-AS3	VIA, VIB	Dual Driver		8 V			
3 V VDDI Ordering Option	ons							
Si8237AB-D-IS1	Si8237AB-AS1	VIA, VIB	Dual Driver	0.5 A	5 V			
Si8237BB-D-IS1	Si8237BB-AS1	VIA, VIB	Dual Driver	0.5 A	8 V	2510/1000	SOIC-16	
Si8238AB-D-IS1	Si8238AB-AS1	VIA, VIB	Dual Driver	4.0 A	5 V	2.5 kVrms	Narrow Body	
Si8238BB-D-IS1	Si8238BB-AS1	VIA, VIB	Dual Driver	4.0 A	8 V			
Si8237AC-D-IS1	Si8237AC-AS1	VIA, VIB	Dual Driver	0 5 4	5 V			
Si8237BC-D-IS1	Si8237BC-AS1	VIA, VIB	Dual Driver	0.5 A	8 V	2 7E W/mm	SOIC-16	
Si8238AC-D-IS1	Si8238AC-AS1	VIA, VIB	Dual Driver	40.4	5 V	3.75 kVrms	Narrow Body	
Si8238BC-D-IS1	Si8238BC-AS1	VIA, VIB	Dual Driver	4.0 A	8 V			

Ordering Part Number (OPN)	Automotive OPN ^{5,6}	Inputs	Configuration	Peak Current	UVLO Voltage	lsolation Rating	Package Type
Si8237AD-D-IS	Si8237AD-AS	VIA, VIB	Dual Driver	05.4	5 V		
Si8237BD-D-IS	Si8237BD-AS	VIA, VIB	Dual Driver	- 0.5 A	8 V		SOIC-16 Wide Body
Si8238AD-D-IS	Si8238AD-AS	VIA, VIB	Dual Driver		5 V		
Si8238BD-D-IS	Si8238BD-AS	VIA, VIB	Dual Driver		8 V 5 V	5.0 kVrms	
Si8238AD-D-IS3	Si8238AD-AS3	VIA, VIB	Dual Driver				SOIC-14
Si8238BD-D-IS3	Si8238BD-AS3	VIA, VIB	Dual Driver		8 V		Wide Body with increased creepage

1. All packages are RoHS-compliant with peak reflow temperatures of 260 °C according to the JEDEC industry standard classifications and peak solder temperatures.

2. "Si" and "SI" are used interchangeably.

3. An "R" at the end of the part number denotes tape and reel packaging option.

4. The temperature ranges is -40 to +125 °C.

5. Automotive-Grade devices (with an "-A" suffix) are identical in construction materials, topside marking, and electrical parameters to their Industrial-Grade (with an "-I" suffix) version counterparts. Automotive-Grade products are produced utilizing full automotive process flows and additional statistical process controls throughout the manufacturing flow. The Automotive-Grade part number is included on shipping labels.

6. In the top markings of each device, the Manufacturing Code represented by either "RTTTTT" or "TTTTTT" contains as its first character a letter in the range N through Z to indicate Automotive-Grade.

Table of Contents

1.	. Ordering Guide	2
2.	. System Overview	8
	2.1 Top Level Block Diagrams	8
	2.2 Functional Description	10
	2.3 Typical Operating Characteristics (0.5 Amp)	11
	2.4 Typical Operating Characteristics (4.0 Amp)	14
	2.5 Family Overview and Logic Operation During Startup	
	2.5.1 Products	
	2.6 Power Supply Connections	
	2.7 Power Dissipation Considerations	
	2.8 Layout Considerations	
	2.9 Undervoltage Lockout Operation	
	2.9.1 Device Startup	
	2.9.2 Undervoltage Lockout	21
	2.9.3 Undervoltage Lockout (UVLO)	
	2.9.4 Control Inputs	
	2.10 Programmable Dead Time and Overlap Protection	
3.	Electrical Specifications	. 24
3.	Electrical Specifications	
	3.1 Test Circuits	27
	3.1 Test Circuits	27 . 33
	3.1 Test Circuits	27 . 33 33
4.	3.1 Test Circuits	27 . 33 33 34
4.	3.1 Test Circuits	27 . 33 33 34
4 . 5 .	3.1 Test Circuits	27 . 33 33 34 . 35
4 . 5 .	3.1 Test Circuits	27 . 33 33 34 . 35 . 41 41
4 . 5 .	3.1 Test Circuits Applications. 4.1 High-Side/Low-Side Driver 4.2 Dual Driver Pin Descriptions Package Outlines 6.1 Package Outline: 16-Pin Wide Body SOIC. 6.2 Package Outline: 14-Pin Wide Body SOIC.	27 . 33 33 34 . 35 . 41 41 43
4 . 5 .	3.1 Test Circuits	27 . 33 33 34 . 35 . 41 41 43 45
4 . 5 .	3.1 Test Circuits Applications. 4.1 High-Side/Low-Side Driver 4.2 Dual Driver 4.2 Dual Driver Pin Descriptions Package Outlines. 6.1 Package Outline: 16-Pin Wide Body SOIC. 6.2 Package Outline: 14-Pin Wide Body SOIC. 6.3 Package Outline: 16-Pin Narrow Body SOIC. 6.4 Package Outline: 14 LD LGA (5 x 5 mm)	27 . 33 33 34 . 35 . 41 41 43 45 46
4 . 5 .	3.1 Test Circuits	27 . 33 33 34 . 35 . 41 41 43 45 46
4. 5. 6.	3.1 Test Circuits Applications. 4.1 High-Side/Low-Side Driver 4.2 Dual Driver 4.2 Dual Driver Pin Descriptions Package Outlines. 6.1 Package Outline: 16-Pin Wide Body SOIC. 6.2 Package Outline: 14-Pin Wide Body SOIC. 6.3 Package Outline: 16-Pin Narrow Body SOIC. 6.4 Package Outline: 14 LD LGA (5 x 5 mm)	27 . 33 33 34 . 35 . 41 41 43 45 46 47
4. 5. 6.	3.1 Test Circuits Applications. 4.1 High-Side/Low-Side Driver 4.2 Dual Driver 4.2 Dual Driver Pin Descriptions Package Outlines 6.1 Package Outline: 16-Pin Wide Body SOIC. 6.2 Package Outline: 14-Pin Wide Body SOIC. 6.3 Package Outline: 16-Pin Narrow Body SOIC. 6.4 Package Outline: 14 LD LGA (5 x 5 mm) 6.5 Package Outline: 14 LD QFN	27 . 33 34 . 35 . 41 41 43 45 46 46 47 48
4. 5. 6.	3.1 Test Circuits	27 . 33 34 . 35 . 41 43 45 46 47 48 48
4. 5. 6.	3.1 Test Circuits Applications. 4.1 High-Side/Low-Side Driver 4.2 Dual Driver 4.2 Dual Driver Pin Descriptions Package Outlines 6.1 Package Outline: 16-Pin Wide Body SOIC. 6.2 Package Outline: 14-Pin Wide Body SOIC. 6.3 Package Outline: 16-Pin Narrow Body SOIC. 6.4 Package Outline: 14-D LGA (5 x 5 mm) 6.5 Package Outline: 14 LD LGA (5 x 5 mm) 6.5 Package Outline: 14 LD QFN 7.1 Land Patterns	27 33 34 34 34 35 34 34 34 34 34 34 34 34 41 43 45 46 47 48 48 49

8.	Top Markings	52
	8.1 Si823x Top Marking (14/16-Pin Wide Body SOIC)	.52
	8.2 Si823x Top Marking (16-Pin Narrow Body SOIC)	.53
	8.3 Si823x Top Marking (14 LD LGA/QFN)	.54
9.	Revision History	55

2. System Overview

2.1 Top Level Block Diagrams




Figure 2.1. Si8230/3 Two-Input High-Side/Low-Side Isolated Drivers




Figure 2.2. Si8231/4 Single-Input High-Side/Low-Side Isolated Drivers




Figure 2.3. Si8232/5/7/8 Dual Isolated Drivers

2.2 Functional Description

The operation of an Si823x channel is analogous to that of an optocoupler and gate driver, except an RF carrier is modulated instead of light. This simple architecture provides a robust isolated data path and requires no special considerations or initialization at start-up. A simplified block diagram for a single Si823x channel is shown in the figure below.




Figure 2.4. Simplified Channel Diagram

A channel consists of an RF Transmitter and RF Receiver separated by a semiconductor-based isolation barrier. Referring to the Transmitter, input A modulates the carrier provided by an RF oscillator using on/off keying. The Receiver contains a demodulator that decodes the input state according to its RF energy content and applies the result to output B via the output driver. This RF on/off keying scheme is superior to pulse code schemes as it provides best-in-class noise immunity, low power consumption, and better immunity to magnetic fields. See the figure below for more details.




Figure 2.5. Modulation Scheme

2.3 Typical Operating Characteristics (0.5 Amp)

The typical performance characteristics depicted in Figure 2.6 Rise/Fall Time vs. Supply Voltage on page 11 through Figure 2.15 Output Source Current vs. Temperature on page 12 are for information purposes only. Refer to Table 3.1 Electrical Characteristics¹ on page 24 for actual specification limits.




Figure 2.6. Rise/Fall Time vs. Supply Voltage




Figure 2.8. Rise/Fall Time vs. Load




Figure 2.7. Propagation Delay vs. Supply Voltage




Figure 2.9. Propagation Delay vs. Load




Figure 2.10. Propagation Delay vs. Temperature




Figure 2.12. Supply Current vs. Supply Voltage




Figure 2.14. Output Source Current vs. Supply Voltage




Figure 2.11. Supply Current vs. Temperature




Figure 2.13. Supply Current vs. Supply Voltage




Figure 2.15. Output Source Current vs. Temperature




Figure 2.16. Output Sink Current vs. Supply Voltage




Figure 2.17. Output Sink Current vs. Temperature

2.4 Typical Operating Characteristics (4.0 Amp)

The typical performance characteristics depicted in Figure 2.18 Rise/Fall Time vs. Supply Voltage on page 14 through Figure 2.27 Output Source Current vs. Temperature on page 15 are for information purposes only. Refer to Table 3.1 Electrical Characteristics¹ on page 24 for actual specification limits.




Figure 2.18. Rise/Fall Time vs. Supply Voltage




Figure 2.20. Rise/Fall Time vs. Load




Figure 2.19. Propagation Delay vs. Supply Voltage




Figure 2.21. Propagation Delay vs. Load




Figure 2.22. Propagation Delay vs. Temperature




Figure 2.24. Supply Current vs. Supply Voltage




Figure 2.26. Output Source Current vs. Supply Voltage




Figure 2.23. Supply Current vs. Temperature




Figure 2.25. Supply Current vs. Supply Voltage




Figure 2.27. Output Source Current vs. Temperature




Figure 2.28. Output Sink Current vs. Supply Voltage




Figure 2.29. Output Sink Current vs. Temperature

2.5 Family Overview and Logic Operation During Startup

The Si823x family of isolated drivers consists of high-side, low-side, and dual driver configurations.

2.5.1 Products

The table below shows the configuration and functional overview for each product in this family.

Table 2.1.	Si823x	Family	Overview
------------	--------	--------	-----------------

Part Number	Configuration	Overlap Protection	Programmable Dead Time	Inputs	Peak Output Cur- rent (A)
Si8230	High-Side/Low-Side	\checkmark	\checkmark	VIA, VIB	0.5
Si8231	High-Side/Low-Side	\checkmark	\checkmark	PWM	0.5
Si8232/7	Dual Driver	—	—	VIA, VIB	0.5
Si8233	High-Side/Low-Side	\checkmark	\checkmark	VIA, VIB	4.0
Si8234	High-Side/Low-Side	\checkmark	\checkmark	PWM	4.0
Si8235/8	Dual Driver	—	—	VIA, VIB	4.0

2.5.2 Device Behavior

The table below consists of truth tables for the Si8230/3, Si8231/4, and Si8232/5/7/8 families.

Ing	outs	VDDI State	Disable	Disable Output		Notes				
VIA	VIB	_		VOA	VOB					
L	L	Powered	L	L	L	Output transition occurs after internal dead time expires.				
L	Н	Powered	L	L	Н	Output transition occurs after internal dead time expires.				
Н	L	Powered	L	Н	L	Output transition occurs after internal dead time expires.				
Н	Н	Powered	L	L	L	Invalid state. Output transition occurs after internal dead time expires.				
X ²	X ²	Unpowered	Х	L	L	Output returns to input state within 7 µs of VDDI power re- storation.				
Х	Х	Powered	Н	L	L	Device is disabled.				
6i8231/4	(PWM In	put High-Side/	Low-Side)	Truth Tal	ble					
PWM	Input	VDDI State	Disable	Ou	tput	Notes				
				VOA	VOB					
l	Н	Powered	L	Н	L	Output transition occurs after internal dead time expires.				
L		Powered	L	L	Н	Output transition occurs after internal dead time expires.				
>	Κ ²	Unpowered	Х	L	L	Output returns to input state within 7 µs of VDDI power re- storation.				
2	Х	Powered	н	L	L	Device is disabled.				
Si8232/5	5/7/8 (Dua	Driver) Truth	Table							
Inp	outs	VDDI State	Disable	Output		Notes				
VIA	VIB			VOA	VOB	-				
L	L	Powered	L	L	L	Output transition occurs immediately (no internal dead time).				
L	Н	Powered	L	L	Н	Output transition occurs immediately (no internal dead time).				
Н	L	Powered	L	Н	L	Output transition occurs immediately (no internal dead time).				
Н	Н	Powered	L	Н	Н	Output transition occurs immediately (no internal dead time).				
X ²	X ²	Unpowered	х	L	L	Output returns to input state within 7 μ s of VDDI power restoration.				
	x	Powered	Н	L	L	Device is disabled.				

1. This truth table assumes VDDA and VDDB are powered. If VDDA and VDDB are below UVLO, see 2.9 Undervoltage Lockout Operation for more information.

2. Note that an input can power the input die through an internal diode if its source has adequate current.

2.6 Power Supply Connections

Isolation requirements mandate individual supplies for VDDI, VDDA, and VDDB. The decoupling caps for these supplies must be placed as close to the VDD and GND pins of the Si823x as possible. The optimum values for these capacitors depend on load current and the distance between the chip and the regulator that powers it. Low effective series resistance (ESR) capacitors, such as Tantalum, are recommended.

2.7 Power Dissipation Considerations

Proper system design must assure that the Si823x operates within safe thermal limits across the entire load range. The Si823x total power dissipation is the sum of the power dissipated by bias supply current, internal parasitic switching losses, and power dissipated by the series gate resistor and load. Equation 1 shows total Si823x power dissipation.

$$P_{D} = (V_{DDI})(I_{DDI}) + 2(I_{DD2})(V_{DD2}) + \left(f\right)\left(Q_{G}\right)\left(V_{DD2}\right)\left[\frac{R_{P}}{R_{P} + R_{G}}\right] + \left(f\right)\left(Q_{G}\right)\left(V_{DD2}\right)\left[\frac{R_{N}}{R_{N} + R_{G}}\right] + 2fCintV_{DD2}^{2}$$

where:

P_D is the total Si823x device power dissipation (W)

I_{DDI} is the input-side maximum bias current (3 mA)

I_{DD2} is the driver die maximum bias current (2.5 mA)

C_{int} is the internal parasitic capacitance (75 pF for the 0.5 A driver and 370 pF for the 4.0 A driver)

VDDI is the input-side VDD supply voltage (2.7 to 5.5 V)

V_{DD2} is the driver-side supply voltage (10 to 24 V)

f is the switching frequency (Hz)

 Q_G is the gate charge of the FET being driven

R_G is the external gate resistor

 R_P is the $R_{DS(ON)}$ of the driver pull-up switch: ($Rp = 15 \Omega$ for the 0.5 A driver; $Rp = 2.7 \Omega$ for the 4.0 A driver)

 R_N is the $R_{DS(ON)}$ of the driver pull-down switch: (Rn = 5 Ω for the 0.5 A driver and 1 Ω for the 4.0 A driver)

Equation 1

Power dissipation example for 0.5 A driver using Equation 1 with the following givens:

V_{DD1} = 5.0 V

V_{DD2} = 12 V

f = 350 kHz

R_G = 22 Ω

Q_G = 25 nC

 $Pd = 0.015 + 0.060 + (350 \times 10^{3})(25 \times 10^{-9})(12)(\frac{5}{5+22}) + (350 \times 10^{3})(25 \times 10^{-9})(12)(\frac{15}{15+22}) + 2[(350 \times 10^{3})(75 \times 10^{-12})(144)] = 145 \text{ mW}$

From which the driver junction temperature is calculated using Equation 2, where:

Pd is the total Si823x device power dissipation (W)

θja is the thermal resistance from junction to air (105 °C/W in this example)

T_A is the ambient temperature

$$T_i = P_d \times \Theta_{ia} \times T_A = (0.145)(105) + 20 = 35.2 \circ C$$

The maximum power dissipation allowable for the Si823x is a function of the package thermal resistance, ambient temperature, and maximum allowable junction temperature, as shown in Equation 2:

$$P_{Dmax} \le \frac{T_{jmax} - T_A}{\Theta ja}$$

where:

P_{Dmax} = Maximum Si823x power dissipation (W)

T_{imax} = Si823x maximum junction temperature (150 °C)

 T_A = Ambient temperature (20 °C)

Oja = Si823x junction-to-air thermal resistance (105 °C/W)

Equation 2

Substituting values for $P_{Dmax} T_{jmax}$, T_A , and θ_{ja} into Equation 2 results in a maximum allowable total power dissipation of 1.29 W. Maximum allowable load is found by substituting this limit and the appropriate data sheet values from Table 3.1 Electrical Characteristics¹ on page 24 into Equation 1 and simplifying. The result is Equation 3 (0.5 A driver) and Equation 4 (4.0 A driver), both of which assume VDDI = 5 V and VDDA = VDDB = 18 V.


$$Q_{G(MAX)} = \frac{0.164}{f} - 3.05 \times 10^{-9}$$

Equation 3

$$Q_{G(MAX)} = \frac{0.634}{f} - 5.81 \times 10^{-9}$$

Equation 4

Equation 3 and Equation 4 are graphed in the figure below, where the points along the load line represent the package dissipationlimited value of CL for the corresponding switching frequency.



2.8 Layout Considerations

It is most important to minimize ringing in the drive path and noise on the Si823x VDD lines. Care must be taken to minimize parasitic inductance in these paths by locating the Si823x as close to the device it is driving as possible. In addition, the VDD supply and ground trace paths must be kept short. For this reason, the use of power and ground planes is highly recommended. A split ground plane system having separate ground and VDD planes for power devices and small signal components provides the best overall noise performance.

2.9 Undervoltage Lockout Operation

Device behavior during start-up, normal operation and shutdown is shown in Figure 2.30 Device Behavior during Normal Operation and Shutdown on page 21, where UVLO+ and UVLO- are the positive-going and negative-going thresholds respectively. Note that outputs VOA and VOB default low when input side power supply (VDDI) is not present.

2.9.1 Device Startup

Outputs VOA and VOB are held low during power-up until VDD is above the UVLO threshold for time period tSTART. Following this, the outputs follow the states of inputs VIA and VIB.

2.9.2 Undervoltage Lockout

Undervoltage Lockout (UVLO) is provided to prevent erroneous operation during device startup and shutdown or when VDD is below its specified operating circuits range. The input (control) side, Driver A and Driver B, each have their own undervoltage lockout monitors.

The Si823x input side enters UVLO when VDDI \leq VDDI_{UV-}, and exits UVLO when VDDI > VDDI_{UV+}. The driver outputs, VOA and VOB, remain low when the input side of the Si823x is in UVLO and their respective VDD supply (VDDA, VDDB) is within tolerance. Each driver output can enter or exit UVLO independently. For example, VOA unconditionally enters UVLO when VDDA falls below VDDA_{UV-} and exits UVLO when VDDA rises above VDDA_{UV+}.




Figure 2.30. Device Behavior during Normal Operation and Shutdown

2.9.3 Undervoltage Lockout (UVLO)

The UVLO circuit unconditionally drives VO low when VDD is below the lockout threshold. Upon power up, the Si823x is maintained in UVLO until VDD rises above VDD_{UV+}. During power down, the Si823x enters UVLO when VDD falls below the UVLO threshold plus hysteresis (i.e., VDD \leq VDD_{UV+} – VDD_{HYS}).

2.9.4 Control Inputs

VIA, VIB, and PWM inputs are high-true, TTL level-compatible logic inputs. A logic high signal on VIA or VIB causes the corresponding output to go high. For PWM input versions (Si8231/4), VOA is high and VOB is low when the PWM input is high, and VOA is low and VOB is high when the PWM input is low.

2.9.5 Disable Input

When brought high, the DISABLE input unconditionally drives VOA and VOB low regardless of the states of VIA and VIB. Device operation terminates within tSD after DISABLE = V_{IH} and resumes within tRESTART after DISABLE = V_{IL} . The DISABLE input has no effect if VDDI is below its UVLO level (i.e., VOA, VOB remain low).

2.10 Programmable Dead Time and Overlap Protection

All high-side/low-side drivers (Si8230/1/3/4) include programmable overlap protection to prevent outputs VOA and VOB from being high at the same time. These devices also include programmable dead time, which adds a user-programmable delay between transitions of VOA and VOB. When enabled, dead time is present on all transitions, even after overlap recovery. The amount of dead time delay (DT) is programmed by a single resistor (RDT) connected from the DT input to ground per Equation 5. Note that the dead time pin can be tied to VDDI or left floating to provide a nominal dead time at approximately 400 ps.

DT ≈ 10 × RDT

where:

DT = dead time (ns) and

RDT = dead time programing resistor (k Ω)

Equation 5

The device driving VIA and VIB should provide a minimum dead time of TDD to avoid activating overlap protection. Input/output timing waveforms for the two-input drivers are shown in Figure 2.31 Input / Output Waveforms for High-Side / Low-Side Two-Input Drivers on page 22, and dead time waveforms are shown in Figure 2.32 Dead Time Waveforms for High-Side / Low-Side Two-input Drivers on page 23.






Figure 2.31. Input / Output Waveforms for High-Side / Low-Side Two-Input Drivers





3. Electrical Specifications

Table 3.1. Electrical Characteristics¹

$2.7 \text{ V} < \text{VDDI} < 5.5 \text{ V}, \text{VDDA} = \text{VDDB} = 12 \text{ V} \text{ or } 15 \text{ V}, \text{ TA} = -40 \text{ to } +125 \text{ °C}, \text{ Typical specs at } 25 \text{ °C}, \text{ T}_{\text{J}} = -40 \text{ to } +150 \text{ °C}$

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
DC Specifications						
Input-side Power Supply	VDDI	Si8230/1/2/3/4/5	4.5		5.5	V
Voltage		Si8237/8	2.7	_	5.5	
Driver Supply Voltage	VDDA, VDDB	Voltage between VDDA and GNDA, and VDDB and GNDB (See 1. Ordering Guide)	6.5	—	24	V
Input Supply Quiescent	IDDI(Q)	Si8230/2/3/5/7/8	—	2	3	mA
Current		Si8231/4	—	3.5	5	mA
Output Supply Quiescent Current	IDDA(Q), IDDB(Q)	Current per channel	_	_	3.0	mA
Input Supply Active Current	IDDI	Input freq = 500 kHz, no load	—	3.5	_	mA
Output Supply Active Current	IDDA	Current per channel with	—	6	_	mA
	IDDB	Input freq = 500 kHz, no load				
Input Pin Leakage Current	IVIA, IVIB, IPWM		-10	_	+10	µA dc
Input Pin Leakage Current (Si8230/1/2/3/4/5)	IDISABLE		-10	_	+10	µA dc
Input Pin Leakage Current (Si8237/8)			-1000		+1000	
Logic High Input Threshold	VIH		2.0	_	_	V
Logic Low Input Threshold	VIL		—	—	0.8	V
Input Hysteresis	VI _{HYST}	Si8230/1/2/3/4/5/7/8	400	450	_	mV
Logic High Output Voltage	VOAH, VOBH	IOA, IOB = -1 mA	(VDDA / VDDB) — 0.04	—	-	V
Logic Low Output Voltage	VOAL, VOBL	IOA, IOB = 1 mA	—		0.04	V
Output Short-Circuit Pulsed Sink Current	IOA(SCL), IOB(SCL)	Si8230/1/2/7, Figure 3.1 IOL Sink Current Test Circuit on page 27	_	0.5	-	A
		Si8233/4/5/8, Figure 3.1 IOL Sink Current Test Circuit on page 27	_	4.0	-	A
Output Short-Circuit Pulsed Source Current	IOA(SCH), IOB(SCH)	Si8230/1/2/7, Figure 3.2 IOH Source Current Test Circuit on page 27	-	0.25	-	A
		Si8233/4/5/8, Figure 3.2 IOH Source Current Test Circuit on page 27	-	2.0	-	A

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Output Sink Resistance	R _{ON(SINK)}	Si8230/1/2/7	_	5.0	—	Ω
		Si8233/4/5/8	_	1.0	_	Ω
Output Source Resistance	R _{ON(SOURCE)}	Si8230/1/2/7	_	15	_	Ω
		Si8233/4/5/8	—	2.7	—	Ω
VDDI Undervoltage Threshold	VDDI _{UV+}	VDDI rising (Si8230/1/2/3/4/5)	3.60	4.0	4.45	V
VDDI Undervoltage Threshold	VDDI _{UV-}	VDDI falling	3.30	3.70	4.15	V
		(Si8230/1/2/3/4/5)				
VDDI Lockout Hysteresis	VDDI _{HYS}	(Si8230/1/2/3/4/5)	—	250	—	mV
VDDI Undervoltage Threshold	VDDI _{UV+}	VDDI rising (Si8237/8)	2.15	2.3	2.5	V
VDDI Undervoltage Threshold	VDDI _{UV-}	VDDI falling (Si8237/8)	2.10	2.22	2.40	V
VDDI Lockout Hysteresis	VDDI _{HYS}	(Si8237/8)	_	75	_	mV
VDDA, VDDB Undervoltage Threshold	VDDA _{UV+} , VDDB _{UV+}	VDDA, VDDB rising				
5 V Threshold			5.20	5.80	6.30	V
8 V Threshold			7.50	8.60	9.40	V
10 V Threshold			9.60	11.1	12.2	V
12.5 V Threshold			12.4	13.8	14.8	V
VDDA, VDDB Undervoltage Threshold	VDDA _{UV-} , VDDB _{UV-}	VDDA, VDDB falling				
5 V Threshold			4.90	5.52	6.0	V
8 V Threshold			7.20	8.10	8.70	V
10 V Threshold			9.40	10.1	10.9	V
12.5 V Threshold			11.6	12.8	13.8	V
VDDA, VDDB Lockout Hysteresis	VDDA _{HYS} , VDDB _{HYS}	UVLO voltage = 5 V	—	280	_	mV
VDDA, VDDB Lockout Hysteresis	VDDA _{HYS} , VDDB _{HYS}	UVLO voltage = 8 V		600	_	mV
VDDA, VDDB Lockout Hysteresis	VDDA _{HYS} , VDDB _{HYS}	UVLO voltage = 10 V or 12.5 V	_	1000	-	mV
AC Specifications	1			1	1	
Minimum Pulse Width				10	_	ns
Propagation Delay	t _{PHL} , t _{PLH}	CL = 200 pF	_	30	45	ns
Pulse Width Distortion t _{PLH} - t _{PHL}	PWD		_	-	5.60	ns
Minimum Overlap Time ²	TDD	DT = VDDI, No-Connect		0.4	—	ns


Parameter	Symbol	Test Condition	Min	Тур	Мах	Unit
Programmed Dead Time ³	DT	Figure 2.32 Dead Time Wave- forms for High-Side / Low-Side Two-input Drivers on page 23, RDT = 100 k	730	900	1170	ns
		Figure 2.32 Dead Time Wave- forms for High-Side / Low-Side Two-input Drivers on page 23, RDT = 6 k	55	70	75	ns
Output Rise and Fall Time	t _R ,t _F	C _L = 200 pF (Si8230/1/2/7)	_	—	20	ns
		C _L = 200 pF (Si8233/4/5/8)	_	_	12	ns
Shutdown Time from Disable True	t _{SD}		—	_	60	ns
Restart Time from Disable False	t _{RESTART}		—	—	60	ns
Device Start-up Time	t _{START}	Time from VDD_ = VDD_UV+ to VOA, VOB = VIA, VIB	—	-	40	μs
Common Mode	СМТІ	VIA, VIB, PWM = VDDI or 0 V	20	45	—	kV/µs
Transient Immunity		V _{CM} = 1500 V				
		(see Figure 3.3 Common Mode Transient Immunity Test Circuit on page 28)				


2. TDD is the minimum overlap time without triggering overlap protection (Si8230/1/3/4 only).


3. The largest RDT resistor that can be used is 220 k $\Omega.$

3.1 Test Circuits

Figures Figure 3.1 IOL Sink Current Test Circuit on page 27, Figure 3.2 IOH Source Current Test Circuit on page 27, and Figure 3.3 Common Mode Transient Immunity Test Circuit on page 28 depict sink current, source current, and common-mode transient immunity test circuits, respectively.












Figure 3.3. Common Mode Transient Immunity Test Circuit

Table 3.2. Regulatory Information¹

CSA

The Si823x is certified under CSA Component Acceptance Notice 5A. For more details, see Master Contract Number 232873.

60950-1, 62368-1: Up to 600 V_{RMS} reinforced insulation working voltage; up to 1000 V_{RMS} basic insulation working voltage.

60601-1: Up to 250 V_{RMS} working voltage and 2 MOPP (Means of Patient Protection).

VDE

The Si823x is certified according to VDE 0884-10 and EN 60950-1. For more details, see certificates 40018443, 40030763.

0884-10: Up to 891 Vpeak for basic insulation working voltage.

60950-1: Up to 600 V_{RMS} reinforced insulation working voltage; up to 1000 V_{RMS} basic insulation working voltage.

UL

The Si823x is certified under UL1577 component recognition program. For more details, see File E257455.

Rated up to 5000 V_{RMS} isolation voltage for basic protection.

CQC

The Si823x is certified under GB4943.1-2011. For more details, see certificates CQC13001096106, CQC13001096108, and CQC 17001178087.

Rated up to 600 V_{RMS} reinforced insulation working voltage; up to 1000 V_{RMS} basic insulation working voltage.

Note:

Regulatory Certifications apply to 2.5 kV_{RMS} rated devices which are production tested to 3.0 kV_{RMS} for 1 sec. Regulatory Certifications apply to 3.75 kV_{RMS} rated devices which are production tested to 4.5 kV_{RMS} for 1 sec. Regulatory Certifications apply to 5.0 kV_{RMS} rated devices which are production tested to 6.0 kV_{RMS} for 1 sec. Regulatory Certifications apply to 5.0 kV_{RMS} rated devices which are production tested to 6.0 kV_{RMS} for 1 sec. For more information, see 1. Ordering Guide.

			Value			
Parameter	Symbol Te	Test Condition	WBSOIC-14/16 5 kV _{RMS}	WBSOIC-14/16 NBSOIC-16 2.5 kV _{RMS} / 3.75 kV _{RMS}	14 LD LGA /QFN 2.5 kV _{RMS}	Unit
Nominal External Air Gap (Clearance) ¹	CLR		8.0	8.0/4.01	3.5	mm
Nominal External Track- ing (Creepage) ¹	CPG		8.0	8.0/4.01	3.5	mm
Minimum Internal Gap (Internal Clearance)	DTI		0.014	0.014	0.014	mm
Tracking Resistance	CTI or PTI	IEC60112	600	600	600	V
Erosion Depth	ED		0.019/0.122	0.019/0.122	0.021	mm
Resistance (Input-Output) ²	R _{IO}		10 ¹²	10 ¹²	10 ¹²	Ω
Capacitance (Input-Output) ²	C _{IO}	f = 1 MHz	1.4	1.4	1.4	pF
Input Capacitance ³	CI		4.0	4.0	4.0	pF

Table 3.3. Insulation and Safety-Related Specifications

Notes:

1. The values in this table correspond to the nominal creepage and clearance values as detailed in 6.1 Package Outline: 16-Pin Wide Body SOIC, 6.2 Package Outline: 14-Pin Wide Body SOIC, 6.3 Package Outline: 16-Pin Narrow Body SOIC, 6.4 Package Outline: 14 LD LGA (5 x 5 mm), 6.5 Package Outline: 14 LD QFN. VDE certifies the clearance and creepage limits as 4.7 mm minimum for the NB SOIC and 8.5 mm minimum for the WB SOIC package. UL does not impose a clearance and creepage minimum for component level certifications. CSA certifies the clearance and creepage of the WB SOIC package with designation "IS3" as 8 mm minimum. CSA certifies the clearance and creepage limits as 3.9 mm minimum for the WB SOIC package with package designation "IS" as listed in the data sheet.

2. To determine resistance and capacitance, the Si823x is converted into a 2-terminal device. Pins 1–8 (1–7, 14 LD LGA/QFN) are shorted together to form the first terminal and pins 9–16 (8–14, 14 LD LGA/QFN) are shorted together to form the second terminal. The parameters are then measured between these two terminals.

3. Measured from input pin to ground.

Parameter	Test Condition	Specification		
		WB SOIC-14/16	NB SOIC-16	14 LD LGA/QFN
Basic Isolation Group	Material Group	I	I	Ι
Installation Classification	Rated Mains Voltages < 150 V _{RMS}	I-IV	I-IV	I-IV
	Rated Mains Voltages < 300 V _{RMS}	I-IV	1-111	I-III
	Rated Mains Voltages < 400 V _{RMS}	1-111	I-II	I-II
	Rated Mains Voltages < 600 V _{RMS}	1-111	1-11	I-II

Table 3.4. IEC 60664-1 Ratings

Table 3.5. VDE 0884-10 Insulation Characteristics¹

NB SOIC-16 14 LD LGA/QFN 560	Unit
560) / pook
	V peak
1050	V peak
4000	V peak
3077	V peak
2	
>10 ⁹	Ω
	2

*Note:

1. Maintenance of the safety data is ensured by protective circuits. The Si823x provides a climate classification of 40/125/21.


Parameter	Symbol	Test Condition	WB SOIC-14/16	NB SOIC-16	14 LD LGA/QFN	Unit
Case Temperature	Τ _S		150	150	150	°C
Safety Input Current	IS	$\theta_{JA} = 100 °C/W (WB SO-IC-14/16),105 °C/W (NB SOIC-16,14 LD LGA/QFN)VDDI = 5.5 V,VDDA = VDDB = 24 V,TJ = 150 °C, TA = 25 °C$	50	50	50	mA
Device Power Dissipa- tion ²	P _D		1.2	1.2	1.2	W


Table 3.6. VDE 0884-10 Safety Limiting Values¹

page 31. 2. The Si82xx is tested with V_{DDI} = 5.5 V, V_{DDA} = V_{DDB} = 24 V, T_J = 150 °C, C_L = 100 pF, input 2 MHz 50% duty cycle square wave.

14 LD LGA/QFN Thermal Derating Curve, Dependence of Safety Limiting Values with Case Temperature per VDE 0884-10 on

Parameter	Symbol	WB SOIC-14/16	NB SOIC-16	14 LD LGA/QFN	Unit
IC Junction-to-Air Thermal Resistance	θ _{JA}	100	105	105	°C/W





Parameter	Symbol	Min	Мах	Unit	
Storage Temperature ²	T _{STG}	-65	+150	°C	
Ambient Temperature under Bias	T _A	-40	+125	°C	
Junction Temperature	TJ		+150	°C	
Input-side Supply Voltage	VDDI	-0.6	6.0	V	
Driver-side Supply Voltage	VDDA, VDDB	-0.6	30	V	
Voltage on any Pin with respect to Ground	V _{IO}	-0.5	VDD + 0.5	V	
Output voltage to GND, repeat spike of –2 V for 200 ns, 200 kHz	VOA to GNDA, VOB to GNDB	-2	VDDA/B + 0.5	V	
Peak Output Current (t_{PW} = 10 µs, duty cycle = 0.2%)	Іорк	_	0.5	A	
(0.5 Amp versions)					
Peak Output Current (t_{PW} = 10 µs, duty cycle = 0.2%)	I _{ОРК}	_	4.0	A	
(4.0 Amp versions)					
Lead Solder Temperature (10 s)		_	260	°C	
Maximum Isolation (Input to Out- put) (1 s) WB SOIC		_	6500	V _{RMS}	
Maximum Isolation (Output to Out- put) (1 s) WB SOIC		_	2500	V _{RMS}	
Maximum Isolation (Input to Out- put) (1 s) NB SOIC		_	4500	V _{RMS}	
Maximum Isolation (Output to Out- put) (1 s) NB SOIC		_	2500	V _{RMS}	
Maximum Isolation (Input to Out- put) (1 s) 14 LD LGA/QFN		_	3850	V _{RMS}	
Maximum Isolation (Output to Out- put) (1 s) 14 LD LGA/QFN		_	650	V _{RMS}	

Table 3.8. Absolute Maximum Ratings¹

Notes:

1. Permanent device damage may occur if the absolute maximum ratings are exceeded. Functional operation should be restricted to the conditions as specified in the operational sections of this data sheet. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

2. VDE certifies storage temperature from -40 to 150 °C.

4. Applications

The following examples illustrate typical circuit configurations using the Si823x.

4.1 High-Side/Low-Side Driver

The Figure A in the drawing below shows the Si8230/3 controlled using the VIA and VIB input signals, and Figure B shows the Si8231/4 controlled by a single PWM signal.




Figure 4.1. Si823x in Half-Bridge Application

For both cases, D1 and CB form a conventional bootstrap circuit that allows VOA to operate as a high-side driver for Q1, which has a maximum drain voltage of 1500 V. The boot-strap start up time will depend on the CB cap chosen. See application note, "AN486: High-Side Bootstrap Design Using Si823x ISODrivers in Power Delivery Systems". VOB is connected as a conventional low-side driver, and, in most cases, VDD2 is the same as VDDB. Note that the input side of the Si823x requires VDD in the range of 4.5 to 5.5 V (2.7 to 5.5 V for Si8237/8), while the VDDA and VDDB output side supplies must be between 6.5 and 24 V with respect to their respective grounds. It is recommended that bypass capacitors of 0.1 and 1 μ F value be used on the Si823x input side and that they be located as close to the chip as possible. Moreover, it is recommended that 0.1 and 10 μ F bypass capacitors, located as close to the chip as possible, be used on the Si823x output side to reduce high-frequency noise and maximize performance.

4.2 Dual Driver

The figure below shows the Si823x configured as a dual driver. Note that the drain voltages of Q1 and Q2 can be referenced to a common ground or to different grounds with as much as 1500 V dc between them.




Figure 4.2. Si8232/5/7/8 in a Dual Driver Application

Because each output driver resides on its own die, the relative voltage polarities of VOA and VOB can reverse without damaging the driver. That is, the voltage at VOA can be higher or lower than that of VOB by VDD without damaging the driver. Therefore, a dual driver in a low-side high side/low side drive application can use either VOA or VOB as the high side driver. Similarly, a dual driver can operate as a dual low-side or dual high-side driver and is unaffected by static or dynamic voltage polarity changes.

5. Pin Descriptions




Table 5.1. Si8230/3 Two-Input HS/LS Isolated Driver (SOIC-16). WB SOIC-14 with IS3 package designation, has pins 12 & 13missing

Pin	Name	Description
1	VIA	Non-inverting logic input terminal for Driver A.
2	VIB	Non-inverting logic input terminal for Driver B.
3	VDDI	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V.
4	GNDI	Input-side ground terminal.
5	DISABLE	Device Disable. When high, this input unconditionally drives outputs VOA, VOB LOW. It is strongly recommended that this input be connected to external logic level to avoid erroneous operation due to capacitive noise coupling.
6	DT	Dead time programming input. The value of the resistor connected from DT to ground sets the dead time between output transitions of VOA and VOB. Defaults to 400 ps dead time when connected to VDDI or left open (see 2.10 Programmable Dead Time and Overlap Protection). If improved noise immunity is desired, a 10 nF capacitor may be added in parallel to the dead time programming resistor (RDT).
7	NC	No connection.
8	VDDI	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V.
9	GNDB	Ground terminal for Driver B.
10	VOB	Driver B output (low-side driver).
11	VDDB	Driver B power supply voltage terminal; connect to a source of 6.5 to 24 V.
12	NC	No connection.
13	NC	No connection.
14	GNDA	Ground terminal for Driver A.
15	VOA	Driver A output (high-side driver).
16	VDDA	Driver A power supply voltage terminal; connect to a source of 6.5 to 24 V.




Table 5.2. Si8231/4 PWM Input HS/LS Isolated Driver (SOIC-16). WB SOIC-14 with IS3 package designation, has pins 12 & 13 missing

Pin	Name	Description
1	PWM	PWM input.
2	NC	No connection.
3	VDDI	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V.
4	GNDI	Input-side ground terminal.
5	DISABLE	Device Disable. When high, this input unconditionally drives outputs VOA, VOB LOW. It is strongly recommended that this input be connected to external logic level to avoid erroneous operation due to capacitive noise coupling.
6	DT	Dead time programming input. The value of the resistor connected from DT to ground sets the dead time between output transitions of VOA and VOB. Defaults to 400 ps dead time when connected to VDDI or left open (see 2.10 Programmable Dead Time and Overlap Protection). If improved noise immunity is desired, a 10 nF capacitor may be added in parallel to the dead time programming resistor (RDT).
7	NC	No connection.
8	VDDI	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V.
9	GNDB	Ground terminal for Driver B.
10	VOB	Driver B output (low-side driver).
11	VDDB	Driver B power supply voltage terminal; connect to a source of 6.5 to 24 V.
12	NC	No connection.
13	NC	No connection.
14	GNDA	Ground terminal for Driver A.
15	VOA	Driver A output (high-side driver).
16	VDDA	Driver A power supply voltage terminal; connect to a source of 6.5 to 24 V.





Table 5.3. Si8232/5/7/8 Dual Isolated Driver (SOIC-16). WB SOIC-14 with IS3 package designation, has pins 12 & 13 missing


Pin	Name	Description
1	VIA	Non-inverting logic input terminal for Driver A.
2	VIB	Non-inverting logic input terminal for Driver B.
3	VDDI	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V, (2.7 to 5.5 V for Si8237/8).
4	GNDI	Input-side ground terminal.
5	DISABLE	Device Disable. When high, this input unconditionally drives outputs VOA, VOB LOW. It is strongly recommended that this input be connected to external logic level to avoid erroneous operation due to capacitive noise coupling.
6	NC	No connection.
7	NC	No connection.
8	VDDI	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V, (2.7 to 5.5 V for Si8237/8).
9	GNDB	Ground terminal for Driver B.
10	VOB	Driver B output.
11	VDDB	Driver B power supply voltage terminal; connect to a source of 6.5 to 24 V.
12	NC	No connection.
13	NC	No connection.
14	GNDA	Ground terminal for Driver A.
15	VOA	Driver A output.
16	VDDA	Driver A power supply voltage terminal; connect to a source of 6.5 to 24 V.



LGA-14 and QFN-14 (5 x 5 mm)

Table 5.4. Si8233 Two-Input HS/LS Isolated Driver (14 LD LGA and QFN)

Pin	Name	Description
GNDI	1	Input-side ground terminal.
VIA	2	Non-inverting logic input terminal for Driver A.
VIB	3	Non-inverting logic input terminal for Driver B.
VDDI	4	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V.
DISABLE	5	Device Disable. When high, this input unconditionally drives outputs VOA, VOB LOW. It is strongly recommended that this input be connected to external logic level to avoid erroneous operation due to capacitive noise coupling.
DT	6	Dead time programming input. The value of the resistor connected from DT to ground sets the dead time between output transitions of VOA and VOB. Defaults to 400 ps dead time when connected to VDDI or left open (see2.10 Programmable Dead Time and Overlap Protection). If improved noise immunity is desired, a 10 nF capacitor may be added in parallel to the dead time programming resistor (RDT).
VDDI	7	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V.
GNDB	8	Ground terminal for Driver B.
VOB	9	Driver B output (low-side driver).
VDDB	10	Driver B power supply voltage terminal; connect to a source of 6.5 to 24 V.
NC	11	No connection.
GNDA	12	Ground terminal for Driver A.
VOA	13	Driver A output (high-side driver).
VDDA	14	Driver A power supply voltage terminal; connect to a source of 6.5 to 24 V.



LGA-14 and QFN-14 (5 x 5 mm)

Table 5.5. Si8234 PWM Input HS/LS Isolated Driver (14 LD LGA and QFN)

Pin	Name	Description
GNDI	1	Input-side ground terminal.
PWM	2	PWM input.
NC	3	No connection.
VDDI	4	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V.
DISABLE	5	Device Disable. When high, this input unconditionally drives outputs VOA, VOB LOW. It is strongly recommended that this input be connected to external logic level to avoid erroneous operation due to capacitive noise coupling.
DT	6	Dead time programming input. The value of the resistor connected from DT to ground sets the dead time between output transitions of VOA and VOB. Defaults to 400 ps dead time when connected to VDDI or left open (see 2.10 Programmable Dead Time and Overlap Protection). If improved noise immunity is desired, a 10 nF capacitor may be added in parallel to the dead time programming resistor (RDT).
VDDI	7	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V.
GNDB	8	Ground terminal for Driver B.
VOB	9	Driver B output (low-side driver).
VDDB	10	Driver B power supply voltage terminal; connect to a source of 6.5 to 24 V.
NC	11	No connection.
GNDA	12	Ground terminal for Driver A.
VOA	13	Driver A output (high-side driver).
VDDA	14	Driver A power supply voltage terminal; connect to a source of 6.5 to 24 V.

			`	,
GNDI	1		14	VDDA
VIA	2		13	VOA
VIB	3		12	GNDA
VDDI	4	Si8235	11	NC
DISABLE	5		10	VDDB
NC	6		9	VOB
VDDI	7		8	GNDB

LGA-14 and QFN-14 (5 x 5 mm)

Table 5.6. Si8235 Dual Isolated Driver (14 LD LGA and QFN)

Pin	Name	Description
GNDI	1	Input-side ground terminal.
VIA	2	Non-inverting logic input terminal for Driver A.
VIB	3	Non-inverting logic input terminal for Driver B.
VDDI	4	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V.
DISABLE	5	Device Disable. When high, this input unconditionally drives outputs VOA, VOB LOW. It is strongly recommended that this input be connected to external logic level to avoid erroneous operation due to capacitive noise coupling.
NC	6	No connection.
VDDI	7	Input-side power supply terminal; connect to a source of 4.5 to 5.5 V.
GNDB	8	Ground terminal for Driver B.
VOB	9	Driver B output (low-side driver).
VDDB	10	Driver B power supply voltage terminal; connect to a source of 6.5 to 24 V.
NC	11	No connection.
GNDA	12	Ground terminal for Driver A.
VOA	13	Driver A output (high-side driver).
VDDA	14	Driver A power supply voltage terminal; connect to a source of 6.5 to 24 V.

6. Package Outlines

6.1 Package Outline: 16-Pin Wide Body SOIC

Figure 6.1 16-Pin Wide Body SOIC on page 41 illustrates the package details for the Si823x in a 16-Pin Wide Body SOIC. Table 6.1 Package Diagram Dimensions on page 41 lists the values for the dimensions shown in the illustration.




Figure 6.1. 16-Pin Wide Body SOIC

Table 6.1. Package Diagram Dimensions

Dimension	Min	Мах		
A	—	2.65		
A1	0.10	0.30		
A2	2.05	_		
b	0.31	0.51		
С	0.20	0.33		
D	10.30 BSC			
E	10.30 BSC			
E1	7.50 BSC			
e	1.27 BSC			
L	0.40	1.27		
h	0.25	0.75		
θ	0°	8°		

Dimension	Min	Мах
ααα	_	0.10
bbb	_	0.33
CCC	_	0.10
ddd		0.25
eee		0.10
fff		0.20
Notos:	I	

Notes:

1. All dimensions shown are in millimeters (mm) unless otherwise noted.

2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.

3. This drawing conforms to JEDEC Outline MS-013, Variation AA.

4. Recommended reflow profile per JEDEC J-STD-020 specification for small body, lead-free components.

6.2 Package Outline: 14-Pin Wide Body SOIC

Figure 6.2 Si823x 14-pin WB SOIC Outline on page 43 illustrates the package details for the Si823x in a 14-Pin Wide Body SOIC. Table 6.2 Package Diagram Dimensions on page 43 lists the values for the dimensions shown in the illustration.




Figure 6.2. Si823x 14-pin WB SOIC Outline

Table 6.2. Package Diagram Dimensions

Dimension	MIN	МАХ
A	_	2.65
A1	0.10	0.30
A2	2.05	—
b	0.31	0.51
с	0.20	0.33
D	10.30	BSC
E	10.30	BSC
E1	7.50	BSC
e	1.27	BSC
L	0.40	1.27
h	0.25	0.75
Θ	0°	8°
ааа	_	0.10
bbb	_	0.33
ccc	—	0.10
ddd	_	0.25
eee	-	0.10
fff	_	0.20

Si823x Data Sheet Package Outlines

Dimension	MIN	МАХ			
Notes:					
1. All dimensions shown are in millimeters (mm) unless otherwise noted.					
2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.					
3. This drawing conforms to JEDEC Outline MS-013, Variation AA.					
4. Recommended reflow profile per JEDEC J-STD-020 specification for small body, lead-free components.					

6.3 Package Outline: 16-Pin Narrow Body SOIC

Figure 6.3 16-pin Small Outline Integrated Circuit (SOIC) Package on page 45 illustrates the package details for the Si823x in a 16-pin narrow-body SOIC. Table 6.3 Package Diagram Dimensions on page 45 lists the values for the dimensions shown in the illustration.




Figure 6.3. 16-pin Small Outline Integrated Circuit (SOIC) Package

Dimension	Min	Мах		Dimension	Min	Max
A	—	1.75		L	0.40	1.27
A1	0.10	0.25		L2	0.25 BS	С
A2	1.25	—		h	0.25	0.50
b	0.31	0.51		θ	0°	8°
С	0.17	0.25		ааа	0.10	
D	9.90 BSC			bbb	0.20	
E	6.00 BSC			ссс	0.10	
E1	3.90 BSC		1	ddd	0.25	
e	1.27 BSC		1		·	

Table 6.3. Package Diagram Dimensions

Notes:

1. All dimensions shown are in millimeters (mm) unless otherwise noted.

2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.

3. This drawing conforms to the JEDEC Solid State Outline MS-012, Variation AC.

4. Recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

6.4 Package Outline: 14 LD LGA (5 x 5 mm)

Figure 6.4 Si823x LGA Outline on page 46 illustrates the package details for the Si823x in an LGA outline. Table 6.4 Package Diagram Dimensions on page 46 lists the values for the dimensions shown in the illustration.




Figure 6.4. Si823x LGA Outline

Table 6.4. Package Diagram Dimensions

Dimension	MIN	NOM	MAX	
A	0.74	0.84	0.94	
b	0.25	0.30	0.35	
D		5.00 BSC		
D1		4.15 BSC		
e		0.65 BSC		
E	5.00 BSC			
E1		3.90 BSC		
L	0.70	0.75	0.80	
L1	0.05	0.10	0.15	
aaa	_		0.10	
bbb			0.10	
CCC			0.08	
ddd	_	_	0.15	
eee	_		0.08	
Notes:			1	

Notes:

1. All dimensions shown are in millimeters (mm) unless otherwise noted.

2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.

6.5 Package Outline: 14 LD QFN

Figure 6.5 Si823x 14-pin LD QFN Outline on page 47 illustrates the package details for the Si823x in an QFN outline. Table 6.5 Package Diagram Dimensions on page 47 lists the values for the dimensions shown in the illustration.




Figure 6.5. Si823x 14-pin LD QFN Outline

Table 6.5.	Package	Diagram	Dimensions
------------	---------	---------	------------

Dimension	MIN	NOM	МАХ
A	0.74	0.85	0.90
A1	0	0.025	0.05
b	0.25	0.30	0.35
D		5.00 BSC	
e	0.65 BSC		
E	5.00 BSC		
E1	3.60 BSC		
L	0.50	0.60	0.70
L1 ³	_	0.10 BSC	_
ссс	—	_	0.08
ddd	_	_	0.10
			•

Notes:

1. All dimensions shown are in millimeters (mm) unless otherwise noted.

2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.

3. L1 shall not be less than 0.01 mm.

7. Land Patterns

7.1 Land Pattern: 16-Pin Wide Body SOIC

Figure 7.1 16-Pin SOIC Land Pattern on page 48 illustrates the recommended land pattern details for the Si823x in a 16-pin widebody SOIC. Table 7.1 16-Pin Wide Body SOIC Land Pattern Dimensions on page 48 lists the values for the dimensions shown in the illustration.




Figure 7.1. 16-Pin SOIC Land Pattern

Table 7.1. 16-Pin Wide Body SOIC Land Pattern Dimensions

Dimension	Feature	(mm)
C1	Pad Column Spacing	9.40
E	Pad Row Pitch	1.27
X1	Pad Width	0.60
Y1	Pad Length	1.90
Notos:	1	1

Notes:

1. This Land Pattern Design is based on IPC-7351 pattern SOIC127P1032X265-16AN for Density Level B (Median Land Protrusion).

2. All feature sizes shown are at Maximum Material Condition (MMC) and a card fabrication tolerance of 0.05 mm is assumed.

7.2 Land Pattern: 14-Pin Wide Body SOIC

Figure 7.2 14-Pin WB SOIC Land Pattern on page 49 illustrates the recommended land pattern details for the Si823x in a 14-pin Wide Body SOIC. Table 7.2 14-Pin WB SOIC Land Pattern Dimensions on page 49 lists the values for the dimensions shown in the

illustration.




Figure 7.2. 14-Pin WB SOIC Land Pattern

Table 7.2. 14-Pin WB SOIC Land Pattern Dimensions

Dimension	Feature	(mm)
C1	Pad Column Spacing	9.70
E	Pad Row Pitch	1.27
X1	Pad Width	0.60
¥1	Pad Length	1.60

Notes:

1. This Land Pattern Design is based on IPC-7351 pattern SOIC127P1032X265-16AN for Density Level B (Median Land Protrusion).

2. All feature sizes shown are at Maximum Material Condition (MMC) and a card fabrication tolerance of 0.05 mm is assumed.

7.3 Land Pattern: 16-Pin Narrow Body SOIC

Figure 7.3 16-Pin Narrow Body SOIC PCB Land Pattern on page 50 illustrates the recommended land pattern details for the Si823x in a 16-pin narrow-body SOIC. Table 7.3 16-Pin Narrow Body SOIC Land Pattern Dimensions on page 50 lists the values for the dimensions shown in the illustration.




Figure 7.3. 16-Pin Narrow Body SOIC PCB Land Pattern

Table 7.3.	16-Pin Narrow Bod	v SOIC Land Patt	ern Dimensions
10010 1101		y 0010 Euliu i u u	

Dimension	Feature	(mm)
C1	Pad Column Spacing	5.40
E	Pad Row Pitch	1.27
X1	Pad Width	0.60
Y1	Pad Length	1.55
Notes:		1

1. This Land Pattern Design is based on IPC-7351 pattern SOIC127P600X165-16N for Density Level B (Median Land Protrusion).

2. All feature sizes shown are at Maximum Material Condition (MMC) and a card fabrication tolerance of 0.05 mm is assumed.

7.4 Land Pattern: 14 LD LGA/QFN

Figure 7.4 14-Pin LGA/QFN Land Pattern on page 51 illustrates the recommended land pattern details for the Si823x in a 14-pin LGA/QFN. Table 7.4 14-Pin LGA/QFN Land Pattern Dimensions on page 51 lists the values for the dimensions shown in the illustration.




Figure 7.4. 14-Pin LGA/QFN Land Pattern

Table 7.4.	14-Pin I	LGA/QFN	Land	Pattern	Dimensions
------------	----------	---------	------	---------	------------

Dimension	(mm)
C1	4.20
E	0.65
X1	0.80
Y1	0.40

Notes:

General

- 1. All dimensions shown are in millimeters (mm).
- 2. This Land Pattern Design is based on the IPC-7351 guidelines.
- 3. All dimensions shown are at Maximum Material Condition (MMC). Least Material Condition (LMC) is calculated based on a Fabrication Allowance of 0.05 mm.

Solder Mask Design

1. All metal pads are to be non-solder mask defined (NSMD). Clearance between the solder mask and the metal pad is to be 60 µm minimum, all the way around the pad.

Stencil Design

- 1. A stainless steel, laser-cut and electro-polished stencil with trapezoidal walls should be used to assure good solder paste release.
- 2. The stencil thickness should be 0.125 mm (5 mils).
- 3. The ratio of stencil aperture to land pad size should be 1:1.

Card Assembly

- 1. A No-Clean, Type-3 solder paste is recommended.
- 2. The recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

8. Top Markings

8.1 Si823x Top Marking (14/16-Pin Wide Body SOIC)






Table 8.1. Top Marking Explanation (14/16-Pin Wide Body SOIC)

Line 1 Marking:	Base Part Number	Si823 = ISOdriver product series
	Ordering Options	Y = Peak output current
	See Ordering Guide for more information.	0, 1, 2, 7 = 0.5 A
		3, 4, 5, 8 = 4.0 A
		U = UVLO level
		A = 5 V; B = 8 V; C = 10 V; D = 12.5 V
		V = Isolation rating
		B = 2.5 kV; C = 3.75 kV; D = 5.0 kV
Line 2 Marking:	YY = Year	Assigned by the Assembly House. Corresponds to the year and
	WW = Workweek	workweek of the mold date.
	TTTTTT = Mfg Code	Manufacturing Code from Assembly Purchase Order form.
Line 3 Marking:	Circle = 1.5 mm Diameter	"e4" Pb-Free Symbol
	(Center Justified)	
	Country of Origin	TW = Taiwan (as shown), TH = Thailand
	ISO Code Abbreviation	



Line 1 Marking:	Base Part Number	Si823 = ISOdriver product series
	Ordering Options	Y = Peak output current
	See Ordering Guide for more information.	0, 1, 2, 7 = 0.5 A
		3, 4, 5, 8 = 4.0 A
		U = UVLO level
		A = 5 V; B = 8 V; C = 10 V; D = 12.5 V
		V = Isolation rating
		A = 1.0 kV; B = 2.5 kV; C = 3.75 kV
Line 2 Marking:	YY = Year	Assigned by the Assembly House. Corresponds to the year and
	WW = Workweek	workweek of the mold date.
	TTTTTT = Mfg Code	Manufacturing Code from Assembly Purchase Order form.

8.3 Si823x Top Marking (14 LD LGA/QFN)



Line 1 Marking:	Base Part Number	Si823 = ISOdriver product series
	Ordering Options	Y = Peak output current
	See Ordering Guide for more information.	0, 1, 2 = 0.5 A
		3, 4, 5 = 4.0 A
Line 2 Marking:	Ordering options	U = UVLO level
		A = 5 V; B = 8 V; C = 10 V; D = 12.5 V
		V = Isolation rating
		A = 1.0 kV; B = 2.5 kV; C = 3.75 kV
		I = -40 to +125 °C ambient temperature range
		M = LGA package type
		M1 = QFN package type
Line 3 Marking:	ТТТТТТ	Manufacturing Code from Assembly
Line 4 Marking:	Circle = 1.5 mm diameter	Pin 1 identifier
	YYWW	Manufacturing date code

9. Revision History

Revision 2.15

September 2019

• Updated Section 1. Ordering Guide.

Revision 2.14

June 2019

· Added automotive grade OPN, Si8230BD-AS, to Ordering Guide for Automotive Grade OPNs.

Revision 2.13

September 2018

- Added automotive grade OPNs in Ordering Guide for Automotive Grade OPNs.
- Modified power equations in 2.7 Power Dissipation Considerations.
- Corrected typo for IDISABLE in Table 3.1 Electrical Characteristics¹ on page 24.
- Reformatted Table 3.5 VDE 0884-10 Insulation Characteristics¹ on page 30.
- Added Absolute Max rating of –2V/200 ns on output pins in Table 3.8 Absolute Maximum Ratings¹ on page 32.
- Updated 7.2 Land Pattern: 14-Pin Wide Body SOIC.

Revision 2.12

May 2018

· Updated the Ordering Guide for Automotive-Grade OPN options.

Revision 2.1.1

January 2018

· Added new table to Ordering Guide for Automotive-Grade OPN options.

Revision 2.1

October 2017

- Added IS3 and IM1 packaging options
- Added IEC 62368-1 references throughout
- · Changed max propagation delay spec from 60 ns to 45 ns based on new test limits
- Removed references to IEC 61010
- · Removed references to IEC 60747, replaced with references to VDE 0884-10

Revision 2.0

August 7, 2017

Revision 1.9

July 7, 2017

• Updated 1. Ordering Guide to designate tape and reel packaging option.

Revision 1.8

May 17, 2016

• Converted document from Framemaker to DITA.

Revision 1.7

- Updated 3.1 Test Circuits
 - Added CQC certificate numbers.
- · Updated Table 3.3 Insulation and Safety-Related Specifications on page 29
- Updated Erosion Depth.
- Updated Table 3.5 VDE 0884-10 Insulation Characteristics¹ on page 30
 - Updated V_{PR} for WBSOIC-16.
- Updated Table 3.8 Absolute Maximum Ratings¹ on page 32
 - · Removed Io and added Peak Output Current specifications.
- Updated Equation 1.
- Updated Figure 4.1 Si823x in Half-Bridge Application on page 33.
- Updated Figure 4.2 Si8232/5/7/8 in a Dual Driver Application on page 34.
- Updated Ordering Guide Table 1.1 Si823x Ordering Guide ^{1, 2, 4} on page 2

Revision 1.6

- Updated Table 1.1 Si823x Ordering Guide ^{1, 2, 4} on page 2, Ordering Part Numbers.
- · Added Revision D Ordering Part Numbers.
- · Removed all Ordering Part Numbers of previous revisions.

Revision 1.5

- Updated Table 3.1 Electrical Characteristics¹ on page 24, input and output supply current.
- Added references to AEC-Q100 qualified throughout.
- Changed all 60747-5-2 references to 60747-5-5.
- Added references to CQC throughout.
- · Updated pin descriptions throughout.
 - · Corrected dead time default to 400 ps from 1 ns.
- Updated Table 1.1 Si823x Ordering Guide ^{1, 2, 4} on page 2, Ordering Part Numbers.
 - · Removed moisture sensitivity level table notes.

Revision 1.4

- Updated 1. Ordering Guide.
 - Updated "3 V VDDI Ordering Options".

Revision 1.3

- Added Si8237/8 throughout.
- Updated Table 3.1 Electrical Characteristics¹ on page 24.
- Updated Figure 3.1 IOL Sink Current Test Circuit on page 27.
- UpdatedFigure 3.2 IOH Source Current Test Circuit on page 27.
- Added Figure 3.3 Common Mode Transient Immunity Test Circuit on page 28.
- Updated Si823x Family Truth Table to include notes 1 and 2.
- Updated 2.10 Programmable Dead Time and Overlap Protection.
- · Removed references to Figures 26A and 26B.
- Updated Table 1.1 Si823x Ordering Guide ^{1, 2, 4} on page 2.
- · Added Si8235-BA-C-IS1 ordering part number.
- · Added table note.

Revision 1.2

- Updated 1. Ordering Guide.
 - · Updated moisture sensitivity level (MSL) for all package types.
- Updated Table 3.8 Absolute Maximum Ratings¹ on page 32.
- Added junction temperature spec.
- Updated 3.1 Test Circuits with new notes.
- Updated Figures Figure 2.16 Output Sink Current vs. Supply Voltage on page 13, Figure 2.14 Output Source Current vs. Supply Voltage on page 12, Figure 2.17 Output Sink Current vs. Temperature on page 13, and Figure 2.15 Output Source Current vs. Temperature on page 12 to reflect correct y-axis scaling.
- Updated Figure 4.2 Si8232/5/7/8 in a Dual Driver Application on page 34.
- · Updated .
- Updated 6.1 Package Outline: 16-Pin Wide Body SOIC.
- Updated Table 6.1 Package Diagram Dimensions on page 41.
- Change references to 1.5 kV_{RMS} rated devices to 1.0 kV_{RMS} throughout.
- Updated 2.7 Power Dissipation Considerations.

Revision 1.1

- · Updated .
 - · Updated CMTI specification.
- Updated Table 3.1 Electrical Characteristics¹ on page 24.
 - Updated CMTI specification.
- Updated Table 3.5 VDE 0884-10 Insulation Characteristics¹ on page 30.
- Updated 4.2 Dual Driver.
- Updated 1. Ordering Guide.
- · Replaced pin descriptions on page 1 with chip graphics.

Revision 1.0

- Updated Tables 3.1 Test Circuits, Table 3.3 Insulation and Safety-Related Specifications on page 29, Table 3.4 IEC 60664-1 Ratings on page 30, and Table 3.5 VDE 0884-10 Insulation Characteristics¹ on page 30.
- Updated 1. Ordering Guide.
 - · Added 5 V UVLO ordering options
- Added Device Marking sections.

Revision 0.3


- Moved Sections 2, 3, and 4 to after Section 5.
- Updated Tables Table 5.4 Si8233 Two-Input HS/LS Isolated Driver (14 LD LGA and QFN) on page 38, Table 5.5 Si8234 PWM Input HS/LS Isolated Driver (14 LD LGA and QFN) on page 39.
- Removed Si8230, Si8231, and Si8232 from pinout and from title.
- Updated and added Ordering Guide footnotes.
- Updated UVLO specifications in Table 3.1 Electrical Characteristics¹ on page 24.
- Added PWD and Output Supply Active Current specifications in Table 3.1 Electrical Characteristics¹ on page 24.
- Updated and added typical operating condition graphs in 2.3 Typical Operating Characteristics (0.5 Amp) and 2.4 Typical Operating Characteristics (4.0 Amp).

Revision 0.2

- · Updated all specs to reflect latest silicon revision.
- Updated Table 3.1 Electrical Characteristics¹ on page 24 to include new UVLO options.
- Updated Table 3.8 Absolute Maximum Ratings¹ on page 32 to reflect new maximum package isolation ratings
- Added Figures 34, 35, and 36.
- · Updated Ordering Guide to reflect new package offerings.
- Added "Undervoltage Lockout (UVLO)" section to describe UVLO operation.

Revision 0.11

· Initial release.



Disclaimer

Silicon Labs intends to provide customers with the latest, accurate, and in-depth documentation of all peripherals and modules available for system and software implementers using or intending to use the Silicon Labs products. Characterization data, available modules and peripherals, memory sizes and memory addresses refer to each specific device, and "Typical" parameters provided can and do vary in different applications. Application examples described herein are for illustrative purposes only. Silicon Labs reserves the right to make changes without further notice to the product information, specifications, and descriptions herein, and does not give warranties as to the accuracy or completeness of the included information. Without prior notification, Silicon Labs shall have no liability for the consequences of use of the information supplied in this document. This document does not imply or expressly grant any license to design or fabricate any integrated circuits. The products are not designed or authorized to be used within any FDA Class III devices, applications for which FDA premarket approval is required or Life Support Systems without the specific written consent of Silicon Labs. A "Life Support System" is any product or system intended to support or sustain life and/or health, which, if it fails, can be reasonably expected to result in significant personal injury or death. Silicon Labs products are not designed or authorized for althorized for military applications. Labs product shall not be responsible or liable for any injuries or demages related to use of a Silicon Labs product applications. Silicon Labs resorves and memory addresses and implementers using or interval.

Trademark Information

Silicon Laboratories Inc.®, Silicon Laboratories®, Silicon Labs®, SiLabs® and the Silicon Labs logo®, Bluegiga®, Bluegiga®, Bluegiga Logo®, ClockBuilder®, CMEMS®, DSPLL®, EFM®, EFM32®, EFR, Ember®, Energy Micro, Energy Micro logo and combinations thereof, "the world's most energy friendly microcontrollers", Ember®, EZLink®, EZRadio®, EZRadio®, EZRadio®, Cock&, Gecko OS, Gecko OS, Gecko OS, Gecko OS, Studio, ISOmodem®, Precision32®, ProSLIC®, Simplicity Studio®, SiPHY®, Telegesis, the Telegesis Logo®, USBXpress®, Zentri, the Zentri logo and Zentri DMS, Z-Wave®, and others are trademarks or registered trademarks of Silicon Labs. ARM, CORTEX, Cortex-M3 and THUMB are trademarks or registered trademarks of ARM Holdings. Keil is a registered trademark of ARM Limited. Wi-Fi is a registered trademark of the Wi-Fi Alliance. All other products or brand names mentioned herein are trademarks of their respective holders.



Silicon Laboratories Inc. 400 West Cesar Chavez Austin, TX 78701 USA

http://www.silabs.com