



Ordering code

C3030	WV-F-2XNP	N	L	B	T1	N	XX	L
①	②	③	④	⑤	⑥	⑦	⑧	⑨

① Series No.
 ② Connector type: WV=Vertical
 ③ Mounting type: F=With foot
 ④ No. of circuits
 ⑤ N=Halogen Free
 ⑥ Material: L=LCP
 ⑦ Color: B=Black
 ⑧ Plating code for contacts: T1=Tin-plated/Matter Tin-plated
 ⑨ Plating code for solder tabs: N=Non-plating
 ⑩ Option code: 00=Standard 01=Matter Tin-plated
 ⑪ Packing code: L=Tape & Reel(With cap or Mylar)

SPECIFICATIONS

Current Rating: 5A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 10mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1500V AC/minute
 Pin Material: Brass/Tin-plated&Matter Tin-plated
 Material: LCP,UL94V-0
 Color: Black

Ordering Information & Dimensions

PART NO.	Dimensions		PART NO.	Dimensions	
	A	B		A	B
2X01P	---	6.65	2X07P	18.00	24.65
2X02P	3.00	9.65	2X08P	21.00	27.65
2X03P	6.00	12.65	2X09P	24.00	30.65
2X04P	9.00	15.65	2X10P	27.00	33.65
2X05P	12.00	18.65	2X11P	30.00	36.65
2X06P	15.00	21.65	2X12P	33.00	39.65



燦達電子工業股份有限公司
 JOINT TECH ELECTRONIC IND. CO., LTD.

UNIT	SCALE	SHEET
mm	1 : 1	1 of 3
DRAWN BY	APPROVED BY	
王亮	翁志昇	
2013.09.17	2013.09.17	
GENERAL TOLERANCE		
A2	X. X±0.25	
A1	X. XX±0.15	
A0	X. XXX±0.05	
REV.	DESCRIPTION	DATE

TITLE:	3.00mm PITCH 180° WAFER, MICRO-FIT
DRAW NO.:	
C3030WV-F-2XNPXXXXXXXXXX	REV. A2