

P/N LEGEND





C6350	WV	F	XP	MVO
①	②	③	④	⑤
① Series No.				
② Connector type: WV=Vertical				
③ Mounting type: F=With foot				
④ No. of circuits				
⑤ MVO=M type, Nylon 66,UL94V-0, White				


SPECIFICATIONS

Current Rating: 15A AC,DC
 Voltage Rating: 600V AC,DC
 Temperature Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
 Contact Resistance: 3.5m Ω Max
 Insulation Resistance: 1000M Ω Min
 Withstanding Voltage: 2900V AC/minute
 Pin Material: Brass/Tin-plated
 Material: Nylon 66,UL94V-0
 Color: White

Ordering Information & Dimensions

PART NO.	Dimensions	
	A	B
C6350WV-F-02PMVO	6.35	13.97
C6350WV-F-03PMVO	12.70	20.32
C6350WV-F-04PMVO	19.05	26.67
C6350WV-F-05PMVO	25.40	33.02
C6350WV-F-06PMVO	31.75	39.37
C6350WV-F-08PMVO	44.45	52.07



				 燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.			
UNIT		SCALE	SHEET		TITLE:		
mm		1 : 1	1 of 1		6.35mm PITCH 180° SINGLE ROW WAFER, POLARIZING PEG, MALE TYPE		
DRAWN BY		APPROVED BY		DRAW NO. : C6350WV-F-XP MVO			
李勤		董正一					REV. A2
2006.02.25		2006.02.25					
GENERAL TOLERANCE				ANGLE \pm			
A2	EN1703020002	2017.03.13	賴永強	X.X \pm 0.25			
A1	REVISE	2007.09.14	歐陽小強	X.XX \pm 0.15			
A0	NEW RELEASE	2006.02.25	李勤	X.XXX \pm 0.05			
REV.	DESCRIPTION	DATE	NAME				