



### SPECIFICATION

Poles:2-24

Voltage rating:AC, DC 250V

Current rating:AC, DC, 7A

Withstand voltage:1500V AC min.

Insulation resistance:1000MΩ min.

Temperature range:-25℃~+85℃

Applicable PC board thickness:0.031"~0.063"  
(0.8~1.6mm)

Contact resistance:Initial value 10mΩ max.

After environmental testing 20mΩ max.

Material:Nylon66 UL94V-2

Contact:Brass

Finish:Tin-plated

Color:Nature

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: 5557S-2*XP 方针					
DRAWN: LYF	DATE: 2008-04-07	CLIENT P/N		/			
		UNIT	mm	SCALE	free	⊕	≡
		FILE NO.	Ckmtw-5557-0015	REV.	A		