



**SPECIFICATION**

Poles:2-24  
Voltage rating:AC,DC 250V  
Current rating:AC,DC, 7A  
Withstand voltage:1500V AC/min.  
Insulation resistance:1000MΩ/min.  
Temperature range:-25℃~+85℃  
Applicable PC board thickness:0.031"~0.063" (0.8~1.6mm)  
Contact resistance:Initial value/10mΩ max.  
After environmental testing/20mΩ max.

Material:Nylon66 UL94V-2

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	<b>Ckmtw</b> 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD							
CHECKED:	DATE:	TITLE: <b>5557HP-2*XP</b>							
DRAWN:  LYF	DATE:  2008-04-07	CLIENT P/N		/					
		UNIT	mm	SCALE	free				
		FILE NO.	Ckmtw-5557-0007	REV.	A				