





No. of positions/2\*4.2+1.3±0.30  
 (No. of positions/2-1)\*4.2±0.15



P.C.B LAYOUT

**SPECIFICATION**

Poles:2-24  
 Voltage rating:AC, DC 250V  
 Current rating:AC, DC, 7A  
 Withstand voltage:1500V AC min.  
 Insulation resistance:1000MΩ min.  
 Temperature range:-25℃~+85℃  
 Applicable PC board thickness:0.031"~0.063"  
 (0.8~1.6mm)  
 Contact resistance:Initial value 10mΩ max.  
 After environmental testing 20mΩ max.

Material:Nylon66 UL94V-2

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO.,LTD					
CHECKED:	DATE:	TITLE: 5557R-2*XP					
DRAWN:	DATE:	CLIENT P/N		/			
LYF	2008-04-07	UNIT	mm	SCALE	free	⊕	≡
		FILE NO.	Ckmtw-5557-0011	REV.	A		