





NOTES:

- MATERIAL:  
HOUSING: LCP,UL94V-0,COLOR:BLACK  
CONTACT:COPPER ALLOY  
SHELL:STAINLESS STEEL
- PLATING:  
CONTACT:GOLD FLASH PLATED ON CONTACT AREA;MATTE TIN PLATING ON SOLDER TAILS,WITH ENTIRE CONTACT UNDERPLATED 50u"Min. NICKEL  
SWITCH PIN:GOLD FLASH PLATED ON CONTACT AREA;GOLD FLASH PLATING ON SOLDER TAILS, WITH ENTIRE CONTACT UNDERPLATED 50u"Min. NICKEL  
SHELL:50u"Min.NICKEL UNDERPLATED OVERALL,GOLD FLASH PLATED ON SOLDER TAILS
- ELECTRICAL REQUIREMENTS:  
CURRENT:0.5A  
VOLTAGE:100V  
CONTACT RESISTANCE:100mΩ MAX  
INSULATION RESISTANCE 100 MEGOHMS MIN
- MECHANICAL  
DURABILITY 3000 CYCLES

RECOMMENDED PCB LAYOUT  
GENERAL TOLERANCE ±0.05



PIN NO.	DESCRIPTION
P1#	C1:VCC
P2#	C5:GND
P3#	C2:RST
P4#	C6:VPP
P5#	C3:CLK
P6#	C7:I/O
P7#	POL
P8#/SW	DET



ITEM	PART NAME	QTY	MATERIAL	FINISHING
③	Shell	1	SUS	
②	Terminal	8	COPPER ALLOY	
①	Housing	1	HI-TEMP.PLASIC UL 94V-0	BLACK

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
生					ANGLAR ±5°
效					L ≤ 4 ±0.2
					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5

DSND	DATE	SCALE	MODEL TYPE:
DWN	DATE	N/A	SIM CARD CONN
CHKD	DATE	VIEW: ④	PART NO.:
APPD	DATE	UNIT: mm/in	DWG NO.:
	DATE	SIZE: A4	XKSIM-047
		WEIGHT	SHEET
		1.0g	1/1
			REVISION
			A0

XKB INDUSTRIAL PRECISION CO., LIMITED

www.xkg.cn www.helloxkb.com www.helloxkb.cn

文件工程章