


Recommended P.C.B Layout
General Tolerance±0.05

■ Specifications :

- Voltage rating: 600V AC / DC
- Current rating: 9A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ



Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
2*01	5.40	--	2*07	30.60	25.20
2*02	9.60	4.20	2*08	34.80	29.40
2*03	13.80	8.40	2*09	39.00	33.60
2*04	18.00	12.60	2*10	43.20	37.80
2*05	22.20	16.80	2*11	47.40	42.00
2*06	26.40	21.00	2*12	51.60	46.20

				TOLERANCE UNLESS OTHERWISE			DRAWN	CK tan
				X.	±0.30	X°	±5°	CHKD
				.X	±0.20	.X°	±2°	APPD
				.XX	±0.08	.XX°	±1°	VIEW
A0	MODIFICATION	DRAW	DATE	.XXX	±0.03	.XXX°	±0.5°	

XFCN 兴飞连接器有限公司
CONNECTORS XFCN CONNECTORS CO., LTD.

PRODUCT NAME: **4.20mm Crimp Style Connectors**

PART. NO.: **M4202V-2xXX**

SHEET	1/1
DATE	2010. 4. 12
UNITS	mm
SCALE	1:1
DWG. NO.	009

A
B
C
D
E
F
G

G