


Recommended P.C.B Layout
General Tolerance±0.05

■ Specifications :

- Voltage rating: 600V AC / DC
- Current rating: 9A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥100MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ



Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
2*01	5.40	--	2*07	30.60	25.20
2*02	9.60	4.20	2*08	34.80	29.40
2*03	13.80	8.40	2*09	39.00	33.60
2*04	18.00	12.60	2*10	43.20	37.80
2*05	22.20	16.80	2*11	47.40	42.00
2*06	26.40	21.00	2*12	51.60	46.20

G	AO	MODIFICATION	DRAW	DATE	TOLERANCE UNLESS OTHERWISE			DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.	SHEET	1/1
	VER				X.	±0.30	X°	±5°	CHKD		DATE	2010. 4. 12
					.X	±0.20	.X°	±2°	APPD		PRODUCT NAME	4.20mm Crimp Style Connectors
					.XX	±0.08	.XX°	±1°	VIEW		PART. NO.	M4202V-2xXX
		.XXX	±0.03	.XXX°	±0.5°				SCALE	1:1		
									DWG NO.	009		