





SCHMATIC (NON-SHORTING)



P.C.B LAYOUT
BOTTOM VIEW



ITEM	PART NAME	QTY	MATERIAL	FINISHING	REMARK
④	Terminal	3	Brass (0.30t)	ag Plated	
③	Base	1	Phenolic Resin		
②	Cover	1	Sus	Natural	
①	Keystake	1	Pa66	Black	

RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100mΩ MAX
TRAVEL	2mm
OPERATING FORCE	250±100gf
OPERATING LIFE(CYCLES)	10,000

广东星坤科林股份有限公司

① Keystake

MARK	DESCRIPTION	REVISIONS	DATE	REVISED	APPROVED
生					
效					
日					
期					

文件工程章

DSND	DATE	SCALE: N/A	MODEL TYPE: SLIDE SWITCH
DWN	DATE	VIEW: <input checked="" type="checkbox"/> <input type="checkbox"/>	PART NO.: SS12D07
CHKD	DATE	UNIT: mm/in	DWG NO.: SS12D07XX
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g SHEET 1/1 REVISION A0