

V=RoHS & Lead Free Solderable


Q=Halogen Free

Actuator Type: =Soft <62> / Hard <60, 61>

P=Hard <62 Only>



DTSL-6



F=F S.M.T.

Total Height:

0=2.00mm

1=2.50mm


2=3.10mm

Operating Force: K=Black, 100gf N=Brown, 160gf


R=Red, 260gf


S=White, 320gf Y=Yellow, 520gf

N=Brown, 200gf <Soft actuator 62 Only>









(2)

4

DTS(G)F-60 / DTSF-61 : 3000 pcs DTS(G)L-60 / DTS(G)L-61 : 2700 pcs DTS(G)L-62 / DTS(G)F-62 : 2500 pcs

(1)

3

<Tube>

75 pcs <Tape & Reel>

PACKAGE

DTSGF-61 : 2500 pcs

(1)

(3

(2)

6

(4)

P.C.B. LAYOUT


112




6x6 Thinner Type With Ground Terminal (Pitch 4.0mm)





DTSGF-6



PART NO.	Н
DTSGF-60	2.00
DTSGF-61	2.50
DTSGF-62	3.10







P.C.B. LAYOUT