


SCN CONNECTOR

2.5mm pitch/Board-in Crimp style connectors



This 2.5mm pitch multi-circuit board-in connector meets the needs for high-density mounting on printed circuit boards efficiently and economically. The connector can be used for VCRs, car stereo systems, audio products, and many other consumer-oriented electronic products.

- Housing lances
- · Secure mounting on printed circuit boards
- Two types of contacts

Specifications —

Current rating: 3A AC, DC (AWG #22)
Voltage rating: 250V AC, DC

• Temperature range: -25°C to +85°C

(including temperature rise in applying

electrical current)


• Insulation resistance: 1,000M Ω min. • Withstanding voltage: 800V AC/minute • Applicable wire: AWG #28 to #22


• Applicable PC board thickness: 1.2mm, 1.6mm


- * In using the products, refer to "Handling Precaution for Terminal and Connector" described on our website (Technical documents of Product information page).
- * Contact JST for details.
- * RoHS2 compliance.

Standards -

Recognized E60389







Note: 1. The above figure is the figure viewed from soldering side.

2. Applicable PC board thickness: Type A 1.6mm

Type B 1.6mm and 1.2mm.

3. Tolerances are non-cumulative: ±0.05mm

Type A: 1.0±0.05mm dia.


Type B: 2 to 6 circuits/1.0±0.05mm dia.

7 circuits and more/Hole dimensions differ from the above values. Contact JST for details.

4. Hole dimensions differ according to the kind of PC board and piercing method. The dimensions above should serve as a guideline. Contact JST for details.

SCN CONNECTOR

Contact



Ī	Model No.	Typo	Applicable wire		Insulation O.D.	M-4:	O'tra / rool
	wouel No.	Type	mm²	AWG #	(mm)	Material	Q ty / reer
	SCN-001T-P1.0	Α	0.08~0.33	28~22	0.9~1.7	Phosphor bronze	11,000
	SCN-001T-1.0K	В				Brass	

Material and Finish

Tin-plated (reflow treatment)


RoHS2 compliance
Note: 1. Contact JST if you require shielded wires, thin wires or other special wires.

2. Contact JST for brass products.

	Crimping machine				
Contact		Crimp applicator	Dies	Crimp applicator with dies	
SCN-001T-P1.0	AP-K2N	MKS-L	MK/SCN-001-10	APLMK SCN001-10	
SCN-001T-1.0K		*MKS-SC	SC/SCN-001-10	APLSC SCN001-10	

Note: *Strip-crimp applicator

Housing



C::4-	Model No.	Dimensi	O'tu/bog	
Circuits		Α	В	Q'ty/bag
2	2P-SCN	2.5	6.5	1,000
3	3P-SCN	5.0	9.0	1,000
4	4P-SCN	7.5	11.5	1,000
5	5P-SCN	10.0	14.0	1,000
6	6P-SCN	12.5	16.5	1,000
7	7P-SCN	15.0	19.0	1,000
8	8P-SCN	17.5	21.5	1,000
9	9P-SCN	20.0	24.0	1,000
10	10P-SCN	22.5	26.5	1,000
11	11P-SCN	25.0	29.0	1,000
12	12P-SCN	27.5	31.5	1,000
13	13P-SCN	30.0	34.0	1,000
14	14P-SCN	32.5	36.5	1,000
15	15P-SCN	35.0	39.0	1,000
16	16P-SCN	37.5	41.5	1,000

Material and Finish PA 66, UL94V-0, ivory

RoHS2 compliance

<For reference> As the color identification,

the following alphabet shall be put in the underlined part.

For availability, delivery and minimum order quantity, contact JST.

ex. 2P-SCN-oo

(blank)...ivory

K...black R...red Y...yellow