


13.85	15.0	∅3.0
11.85	13.0	∅3.2
8.35	9.5	∅3.2
7.85	9.0	∅3.3
6.85	8.0	∅3.3
6.35	7.5	∅3.3
5.35	6.5	∅3.3
4.85	6.0	∅3.3
3.85	5.0	∅3.5
3.15	4.3	∅3.5
L(mm)	高度 G(mm)	直径 A(mm)

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60HZ) 60S min.
操作力 Operation force	160±30gf 250±50gf
寿命试验 Operating Life	80,000 cycles
行程 Travels	0.25±0.1mm



电路图

0~3	±0.05	±0.10	±0.20
>3~6	±0.05	±0.10	±0.30
>6~30	±0.10	±0.20	±0.50
>30~120	±0.15	±0.30	±0.80
未注尺寸公差(mm)			

第一视角



设计 Jack Jin	图面 单位 A4 MM
审核 Jacky Zhong	比例 重量
批准 Tony Meng	页码 版次 1/1 A/0

6	机架	冷轧钢带	铜锡	1	
5	接触脚	黄铜	镀银	1	
4	基座	PPA(黑色)		1	
3	簧片	复合银	镀银	1	
2	盖板	冷轧钢带	铜锡	1	
1	按钮	PPA(黑色)		1	
序号	零件名称	材料规格	表面处理	数量	备注

东莞市美韩电子科技有限公司
Dongguan Usakro Electronic Technology Co., Ltd.

1:1	DWG NO.	型号:UK-B0209-2G60-AQ25Y	SIZE A4
1 of 1	PART NO.	规格: 6*6 下支架	VER R