





FREE	LOCK
1 2 3 4 5 6	1 2 3 4 5 6




View A



View A
Scale 1:1



SPECIFICATION	
1.环境温度(Operating Temp)	-20℃~+80℃
2.相对湿度(Working Humidity)	5%~35%
3.额定规格(Rated Value)	DC50V/30mA
4.接触电阻(Contact Resistance)	100mΩ max
5.绝缘电阻(Insulation Resistance)	100MΩ min
6.耐电压(Withstand Voltage)	250Vac/60S
7.动作力(Operating Force)	250±50gf
8.使用寿命(Operating Life)	100,000 cycle



PCB LAYOUT

7	Crochet Hook	1PCS	Carbon Steel
6	Spring	1PCS	Carbon Steel
5	Contact Chip	2PCS	Silver-Coated Copper
4	Terminals	6PCS	Copper plated Silver
3	Panel	1PCS	LCP Natural Color
2	Keypad	1PCS	LCP Black
1	Housing	1PCS	LCP Black
序号 NO.	零件名称 PART NAME	数量 QTY	材质 MATERIAL

东莞市美韩电子科技有限公司
Dongguan Usakro Electronic Technology Co., Ltd.

普通公差 common tolerance		角度angular: ±0.5°	
0~5±0.15;	5~10±0.3;	10~30±0.5;	
DATE	CHECKED	SCALE	料号Part NO.
2018-7-18	JEFF	free	UK-G0701-ZS-Y
APPROVED	JEFF	尺寸 SIZE	
		A4	