


## 本公司智慧財產,未經同意不得複製 DAILYWELL copyright, may not be used without permission from DAILYWELL







	POS.1	POS.2	POS.3		
Model No.		Î <b>F</b>	, A		
2MS1	ON	NONE	ON		
Term. Comm.	2-3	N/A	2-1		
SCHEMATIC	2 Comm. 3	N/A	2 Comm. 03		

SWITCH FUNCTION


	PART NO.	PART NAME	Q'TY
1	MNU-2M01	10-48 INCH NUTS	2
2	MNU-2M03	LOCKWASHER	1

FILE NAME:HARDWARE-0003



		ø.195 ø4.95
-	-	
_ <b>&gt;</b>	-	.179 4.55

PANEL MOUNTING



SOLDER LUG

$\begin{array}{llllllllllllllllllllllllllllllllllll$			hrome plated el plated Steel		Silver 3 Pr Gold over silver 1	amps @120 VAC or 26 Amps @250 VAC 1.4 Volt-Amps(VA) max. @2 份有阼	20V max. (AC or DC) 良公司		
	符號	原尺寸	修改後尺寸	變更日期	SCALE (比例): 3:2	TITLE 圖 名	Sub - Miniature To	ggle Switches	SIZE 圖紙 A4
$\frac{1}{2}$	(A) (B)		操作溫度-30℃修訂為-40℃	MAY-25-2018	TOLERANCE (公差) : 0.00 mm ± 0.25mm	■ □ DWG NO. 圖 號	2MS1T1B1N	/1QES-5	UNIT inch 單位 mm
3	Ô				0.0 mm <u>+</u> 0.40mm	REV. 版本	B DATE AUG	- 25 - 2009	SHEET 張數1 of 1
4 5	D E				ANGULAR : ± 2.54 mm FILE NAME : 2MSP0628	CHECKED BY 審核	陳登財	DRAWN BY 製 圖	IRENE

DAILYWELL

德利威電子股份有限公司

版本:C

表單編號:QR-0507