





环保物料

TEL:0769-82001899

Recommended P.C.B Layout
P.C.B Board Tolerance±0.05

NOTES:

Voltage Rating:250V AC/DC
Current Rating:3.0A AC/DC
Dielectric Withstand Voltage:500V AC/minute
Contact Voltage:20M Max.
Insulation Voltage:1000M Min
Operation temperature:-40 °C to +105 °C
Insulator Material:Polyester.Ul94V-0
Contact Material:Brass
Contact Plating:AuorSn Plated on Nickel Overall



塑胶高度可选 (mm)				常用
H	1.0	1.5	2.0	2.54

Dimension antitheses list				
item	PA	---	PC	L
Standard	6.00	---	3.00	11.50
Alternate	---	---	---	---

				TOLERANCE UNLESS OTHERWISE		DRAWN CK tan		XFCN兴飞连接器有限公司		SHEET 1/1	
				X. ±0.30 X° ±5°		CHKD		CONNECTORS XFCN CONNECTORS CO., LTD.		DATE 2010. 4. 12	
				.X ±0.20 .X° ±2°		APPD		PRODUCT NAME 2.54mm Pin Header Connectors		UNITS mm	
				.XX ±0.08 .XX° ±1°		VIEW		PART. NO. PZ254V-12-XX		SCALE 1:1	
AO				.XXX ±0.03 .XXX° ±0.5°		Φ				DWG NO. 009	
VER		MODIFICATION		DRAW		DATE					