$\left[ \right]$		6 7 8 9 10	/
	环保物料	nded P.C.B Layout	
A			A
	NOTES:		
	Voltage Rating:250V AC/DCImage: Constraint of the state of	$\Phi \Phi \Phi \Phi \Phi \Phi^{-\frac{2}{5}}$	
В			В
	Insulation Voltage:1000M Min Operation temperature:-40 °C to +105 °C	<u> </u>	
		.OF POSITIONS±0.40	
C			С
D	) 2.54*(N	-1)POSITIONS±0.20	D
E		+-DA±0.25 +0.25 ±0.25	Е
	塑胶高度可选(mm) 常用   H 1.0 1.5 2.0 2.54		
	Dimension antitheses list		
F	item     PA     −−−     PC     L       Standard     6.00     −−−     3.00     11.50		F
	Alternate		
	TOLERANCE UNLESS OTHERWISE DRAWN	<u>CK tan</u> <b>XFCN</b> 兴飞连接器有限公司 <sup>™™</sup> 1/1	
G	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	CONNECTORS XFCN CONNECTORS CO., LTD. DATE 2010. 4.12	G
	AO     . XX     ±0.08     . XX°     ±1°     APPD       VER     MODIFICATION     DRAW     DATE     . XXX     ±0.03     . XXX°     ±0.5°     VIEW	PRODUCT NAME 2.54mm Pin Header Connectors UNITS IIIIII   Image: Connectors SCALE 1:1   Image: Connectors PART. NO. PZ254V-12-XX DWG NO.	
	1 2 3 4 5	6 7 8 9 10	$\mathbf{\mathbf{N}}$