

## **SPECIFICATIONS**

### Mechanical

Mating Force: 4.54kgf max. Umating Force: 0.34kgf min. Durability: 500 Cycles

### **Electrical**

Current Rating: 2A

Contact Resistance:  $30m\Omega$  max.

Dielectric Withstanding Voltage: 1000V AC/1min min.

Insulation Resistance:  $5000M\Omega$  min.

## **Physical**


Housing: Thermoplastic, UL 94V-0 rated in Teal 322C Color

Contact: Copper alloy


**Plating:** See "ORDERING INFORMATION" **Operating Temperature:** -55 $^{\circ}$ C to +125 $^{\circ}$ C

#### **D-SUB Connector**

DM Series Right Angle Type, T/H 2.77mm [.109"] Pitch 9 Pos.



# **DRAWING**



# ORDERING INFORMATION

